



GreenPerform Troffer

RC100X LED37S 840 W30L120 IAR OC CAU G3

GreenPerform Troffer, 125 lm/W, 840 neutral white, InterAct Pro

GreenPerform troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrating with all available system: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller, GreenPerform troffer offers additional energy saving and connected features.

Product data

General Information		Operating and Electrical	
Light source replaceable	No	Input Voltage	220 to 240 V
Number of gear units	1 unit	Line Frequency	50 to 60 Hz
Driver included	Yes	Inrush current	22 A
Light source engine type	LED	Inrush time	270 ms
CE mark	CE mark	Power Consumption	31 W
Warranty period	3 years	Power Factor (Fraction)	0.95
Flammability mark	For mounting on normally flammable surfaces	Number of products on MCB of 16 A type B 22	
Glow-wire test	Temperature 600 °C, duration 30 s	Temperature	
Light Technical		Ambient temperature range	-20 to +40 °C
Luminous Flux	3.880 lm	Controls and Dimming	
Correlated Color Temperature (Nom)	4000 K	Dimmable	Yes
Luminous Efficacy (rated) (Nom)	125 lm/W	Control interface	InterAct Pro
Color rendering index (CRI)	80	Constant light output	No
Light source color	840 neutral white	Mechanical and Housing	
Optical cover type	Variable linear-lens array in polycarbonate cover	Housing Material	Metal
		Optic material	Polycarbonate

GreenPerform Troffer

Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Ribbed
Overall length	1,197 mm
Overall width	297 mm
Overall height	46 mm
Dimensions (Height x Width x Depth)	46 x 297 x 1197 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<4
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 h
---------------------------	----------

Application Conditions	
Suitable for random switching	No

Product Data	
Order product name	RC100X LED37S 840 W30L120 IAR OC CAU G3
Full product name	RC100X LED37S 840 W30L120 IAR OC CAU G3
Full product code	911401568741
Local code description	RC100X3784312IA
Order code	911401568741
Material Nr. (12NC)	911401568741
Local order code	RC100X3784312IA
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

