



GreenPerform Highbay Elite

BY718P LED200/CW PSU NB

GreenPerform Highbay Elite, 135 W, 21500 lm, 6500 K, 54°

GreenPerform Highbay Elite is the latest innovation in a successful range of highbay luminaires for high ceiling and industrial applications. The unique finless design has received the iF Design Award 2019 and Reddot Design Award 2019 for its aesthetic appeal. But this versatile luminaire offers a wealth of practical features too, including great light quality, high energy savings, a long lifetime at an affordable price and a wide variety of optics and lumen packages. The Green Perform Highbay Elite luminaire provides options for advanced connectivity with IoT based systems and software applications including the Interact Pro system. If you're looking for a "fit and forget" robust and reliable solution with connectivity advantages, Green Perform Highbay Elite is the smart choice.


Product data

General Information		EU RoHS compliant	
Light source replaceable	No	Yes	
Number of gear units	1 unit		
Driver included	Yes		
Light source engine type	LED		
CE mark	CE mark		
Warranty period	3 years		
Flammability mark	For mounting on normally flammable surfaces		
ENEC mark	-		
Glow-wire test	Temperature 650 °C, duration 30 s		
Light Technical			
Luminous Flux	21,500 lm		
Correlated Color Temperature (Nom)	6500 K		
Luminous Efficacy (rated) (Nom)	159 lm/W		
Color rendering index (CRI)	>80		
Light source color	865 cool daylight		
Optic type	Symmetrical		
Optical cover type	Lens		
Luminaire light beam spread	54°		

GreenPerform Highbay Elite

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	54 A
Inrush time	0.65 ms
Power Consumption	135 W
Power Factor (Fraction)	0.95
Cable	Cable 0.3 m without plug
Number of products on MCB of 16 A type B 6	
Temperature	
Ambient temperature range	-30 to +50 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Gray
Optical cover finish	Frosted
Overall height	95 mm
Overall diameter	450 mm

Dimensional drawing



Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	75,000 hour(s)
Application Conditions	
Maximum dim level	Not applicable
Suitable for random switching	No
Product Data	
Order product name	BY718P LED200/CW PSU NB
Full product name	BY718P LED200/CW PSU NB
Full product code	911401569251
Order code	911401569251
Material Nr. (12NC)	911401569251
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

GreenPerform Highbay Elite

