



# Green Perform Highbay Elite

## BY718P LED200/CW PSU WB

Power supply unit - Symmetrical - Lens - 90°

Following the success of GreenPerform Highbay families, GreenPerform Highbay Elite is a big surprising gift for industry solutions, with big innovative insights embedded. Elite comes with a completely new finless aesthetics design which received the iF Design Award 2019 and Reddot Design Award 2019. Next to a unique look and feel, it also offers higher system efficiency, better light quality, longer lifetime and system-interaction offering with affordable price.

### Product data

General Information		Operating and Electrical	
Lamp colour code	865 cool daylight	Warranty period	3 years
Light source replaceable	No	Constant light output	No
Number of gear units	1 unit	Number of products on MCB	6
Driver/power unit/transformer	PSU [ Power supply unit]	LED engine type	LED
Driver included	Yes	Input voltage	220 to 240 V
Optic type	Symmetrical	Input frequency	50 or 60 Hz
Optical cover/lens type	Lens	Inrush current	54 A
Luminaire light beam spread	90°	Inrush time	0.65 ms
Control interface	-	Power factor (min.)	0.95
Cable	Cable 0.3 m without plug	Controls and Dimming	
Protection class IEC	Safety class I (I)	Dimmable	No
Glow-wire test	650/30 [ Temperature 650 °C, duration 30 s]		
Flammability mark	F [ For mounting on normally flammable surfaces]		
CE mark	CE mark		
ENEC mark	-		

# Green Perform Highbay Elite

## Mechanical and Housing

Housing material	Aluminum die-cast
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Optical cover/lens finish	Frosted
Overall height	95 mm
Overall diameter	450 mm
Colour	Grey

## Approval and Application

Ingress protection code	IP65 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [ 5 J vandal-protected]

## Initial Performance (IEC Compliant)

Initial luminous flux	20000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	145 lm/W
Lamp colour temperature	6500 K
Colour Rendering Index	>80
Initial input power	135 W

Power consumption tolerance	+/-10%
-----------------------------	--------

## Over Time Performance (IEC Compliant)

Median useful life L70B50	75000 h
---------------------------	---------

## Application Conditions


Ambient temperature range	-30 to +50 °C
Maximum dimming level	Not applicable
Suitable for random switching	No

## Product Data

Full product code	911401569351
Order product name	BY718P LED200/CW PSU WB
Order code	01569351
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	911401569351
Net weight (piece)	4.700 kg



## Dimensional drawing



BY718P GreenPerform Highbay Elite

