



Coreline Highbay Gen4

BY121P G4 LED200S/840 PSU WB

Coreline Highbay Gen4, 138 W, 20500 lm, 4000 K, 90°, IP65, IK07

CoreLine Highbay Gen4 delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. A reliable, highly-efficient luminaire with a very long-lifetime, it delivers great energy savings and requires less maintenance. At the same time, CoreLine Highbay is very easy to handle. The luminaire can be installed on your existing grid and the electrical connection is a straightforward task, with no need to open the luminaire and an external IP65 connector. With a choice of two beam angles: narrow and wide beam, you can adjust your lighting plan to suit your exact needs. This range also includes Interact Ready luminaires with integrated wireless communications and integrated movement and daylight sensors. So CoreLine Highbay Gen4 is ready to be used with any Interact connected lighting system.

Product data

General Information		Light Technical	
Light source replaceable	No	Flammability mark	For mounting on easily flammable surfaces
Number of gear units	1 unit	ENEC mark	ENEC mark
Driver included	Yes	Glow-wire test	Temperature 650 °C, duration 30 s
Light source engine type	LED	EU RoHS compliant	Yes
Service tag	Yes		
Value ladder	Performance		
CE mark	CE mark		
Warranty period	5 years		
		Luminous Flux	20,500 lm
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	149 lm/W

Coreline Highbay Gen4

Color rendering index (CRI)	>80
Beam angle of light source	90 x 90 degree(s)
Light source color	840 neutral white
Optic type	Wide beam
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	90°
Unified glare rating CEN	26

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	54 A
Inrush time	0.65 ms
Power Consumption	138 W
Power Factor (Fraction)	0.95
Connection	Connection unit 3-pole
Cable	Cable 0.3 m with connector 3-pole
Number of products on MCB of 16 A type B	8

Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Gray
Optical cover finish	Clear
Overall height	95 mm
Overall diameter	450 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.3 %
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions

Performance ambient temperature Tq	35 °C
Maximum dim level	Not applicable
Suitable for random switching	Yes

Product Data

Order product name	BY121P G4 LED200S/840 PSU WB
Full product name	BY121P G4 LED200S/840 PSU WB
Full product code	871016333568100
Order code	911401570151
Material Nr. (12NC)	911401570151
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163335681
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163335681

Coreline Highbay Gen4

Dimensional drawing

