



CoreLine Highbay

BY121P G3 LED205S/840 PIR WB GR

LED module, system flux 20500 lm, 840 neutral white, Power supply unit (On/Off), Wide beam, Grey

Following the successful introduction of the CoreLine High-bay in 2013, the upgrade to a new generation of LEDs has further improved colour rendering and total cost of ownership. Designed as a replacement for HPI 250/400 W luminaires, CoreLine High-bay offers customers all the benefits of LED lighting – fresh light quality, longer service lifetime, reduced energy consumption and maintenance – from a trusted manufacturer. At the same time, it delivers clear benefits for the installer too. The luminaire can be installed on the existing grid. Electrical connection is straightforward: there is no need to open the luminaire for installation or servicing. And being smaller and lighter than conventional luminaires, it is very easy to handle.

Product data

General Information		Lighting Technology	
Lamp family code	LED205S [LED module, system flux 20500 lm]	CE mark	CE mark
Light source replaceable	No	Warranty period	3 years + 2 years upon registration
Number of gear units	Unit	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	-
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 5 s
Light source engine type	LED	EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	20,500 lm
		Correlated Colour Temperature	4000 K
		Luminous efficacy (rated) (nom.)	130 lm/W
		Colour rendering index (CRI)	≥80

CoreLine Highbay

Beam angle of light source	- degree(s)
Light source colour	840 neutral white
Optic type	Wide beam
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	100°

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	155 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	Cable 0.5 m with cable connector 3-pole
Number of products on MCB of 16 A type B	8

Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	Grey
Optical cover/lens finish	Clear
Overall length	454 mm
Overall width	452 mm

Overall height	152 mm
Overall diameter	452 mm
Dimensions (height x width x depth)	152 x 452 x 454 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L70

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	25%
Suitable for random switching	Yes

Product Data

Order product name	BY121P G3 LED205S/840 PIR WB GR
Full product name	BY121P G3 LED205S/840 PIR WB GR
Full EOC	871016331714400
Order code	31714400
Material no. (12 NC)	911401571241
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8710163317144
Numerator – packs per outer box	1
EAN/UPC - Case	8710163317144

Dimensional drawing



