



# CoreLine Highbay

## BY121P G3 LED205S/865 PIR WB GR

LED module, system flux 20500 lm – 865 cool daylight – Power supply unit – Wide beam – Gray

Following the successful introduction of the CoreLine High-bay in 2013, the upgrade to a new generation of LEDs has further improved color rendering and total cost of ownership. Designed as a replacement for HPI 250/400 W luminaires, CoreLine High-bay offers customers all the benefits of LED lighting – fresh light quality, longer service lifetime, reduced energy consumption and maintenance – from a trusted manufacturer. At the same time, it delivers clear benefits for the installer too. The luminaire can be installed on the existing grid. Electrical connection is straightforward: there is no need to open the luminaire for installation or servicing. And being smaller and lighter than conventional luminaires, it is very easy to handle.

### Product data

General Information			
Number of light sources	1 [ 1 pc]	Connection	CU3 [ Connection unit 3-pole]
Lamp family code	LED205S [ LED module, system flux 20500 lm]	Cable	Cord 0.5 m with cable connector 3-pole
Beam angle of light source	- °	Protection class IEC	Safety class I (I)
Light source colour	865 cool daylight	Glow-wire test	650/5 [ Temperature 650 °C, duration 5 s]
Light source replaceable	No	Flammability mark	F [ For mounting on normally flammable surfaces]
Number of gear units	1 unit	CE mark	CE mark
Driver/power unit/transformer	PSU [ Power supply unit]	ENEC mark	-
Driver included	Yes	Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Optic type	WB [ Wide beam]		
Optical cover/lens type	PC [ Polycarbonate bowl/cover]		
Luminaire light beam spread	100°		
Control interface	-		

## CoreLine Highbay

Constant light output	No
Number of products on MCB	8
EU RoHS compliant	Yes
LED engine type	LED

### Operating and Electrical

Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Control signal voltage	-
Inrush current	53 A
Inrush time	0.3 ms
Power factor (min.)	0.9

### Controls and Dimming

Dimmable	Yes
----------	-----

### Mechanical and Housing

Housing material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Optical cover/lens finish	Clear
Overall length	454 mm
Overall width	452 mm
Overall height	152 mm
Overall diameter	452 mm
Diameter	-
Colour	Gray

### Approval and Application

Ingress protection code	IP65 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [ 2 J reinforced]

### Initial Performance (IEC Compliant)

Initial luminous flux	20500 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	130 lm/W
Init. Corr. Colour Temperature	6500 K
Init. colour rendering index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <5
Initial input power	155 W
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* L70 50,000 h	

### Application Conditions


Ambient temperature range	-30 to +45 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	25%
Suitable for random switching	Yes

### Product Data

Full product code	871016331715100
Order product name	BY121P G3 LED205S/865 PIR WB GR
EAN/UPC – product	8710163317151
Order code	31715100
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	911401571441
Net weight (piece)	4.800 kg



## Dimensional drawing



CoreLine High-bay BY120P/BY121P

## CoreLine Highbay

