PHILIPS

Lighting



GreenPerform Highbay Elite

BY718P LED150/NW PSU WB CAU

GreenPerform Highbay Elite, 102 W, 16300 lm, 4000 K, 90°

GreenPerform Highbay Elite is the latest innovation in a successful range of highbay luminaires for high ceiling and industrial applications. The unique finless design has received the iF Design Award 2019 and Reddot Design Award 2019 for its aesthetic appeal. But this versatile luminaire offers a wealth of practical features too, including great light quality, high energy savings, a long lifetime at an affordable price and a wide variety of optics and lumen packages. The Green Perform Highbay Elite luminaire provides options for advanced connectivity with IoT based systems and software applications including the Interact Pro system. If you're looking for a "fit and forget" robust and reliable solution with connectivity advantages, Green Perform Highbay Elite is the smart choice.

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 30 s

EU RoHS compliant	Yes

Light Technical	
Luminous Flux	16,300 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	160 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Optic type	Symmetrical
Optical cover type	Lens
Luminaire light beam spread	90°

GreenPerform Highbay Elite

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	54 A
Inrush time	0.65 ms
Power Consumption	102 W
Power Factor (Fraction)	0.95
Cable	Cable 3.0 m with plug
Number of products on MCB of 16 A type B	6

Temperature	
Ambient temperature range	-30 to +50 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Gray
Optical cover finish	Frosted
Overall height	95 mm
Overall diameter	415 mm

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I


Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Median useful life L70B50	75,000 hour(s)

Application Conditions	
Maximum dim level	Not applicable
Suitable for random switching	No

Product Data	
Order product name	BY718P LED150/NW PSU WB CAU
Full product name	BY718P LED150/NW PSU WB CAU
Full product code	911401578051
Order code	911401578051
Material Nr. (12NC)	911401578051
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.