



GreenPerform Highbay Elite

BY718P LED300/NW PSD WB CAU

GreenPerform Highbay Elite, 217 W, 32500 lm, 4000 K, DALI, 90°

GreenPerform Highbay Elite is the latest innovation in a successful range of highbay luminaires for high ceiling and industrial applications. The unique finless design has received the iF Design Award 2019 and Reddot Design Award 2019 for its aesthetic appeal. But this versatile luminaire offers a wealth of practical features too, including great light quality, high energy savings, a long lifetime at an affordable price and a wide variety of optics and lumen packages. The Green Perform Highbay Elite luminaire provides options for advanced connectivity with IoT based systems and software applications including the Interact Pro system. If you're looking for a "fit and forget" robust and reliable solution with connectivity advantages, Green Perform Highbay Elite is the smart choice.

Product data


General Information			
Light source replaceable	No	Glow-wire test	Temperature 650 °C, duration 30 s
Number of gear units	2 units	EU RoHS compliant	Yes
Driver included	Yes	Light Technical	
Light source engine type	LED	Luminous Flux	32,500 lm
Service tag	Yes	Correlated Color Temperature (Nom)	4000 K
CE mark	CE mark	Luminous Efficacy (rated) (Nom)	150 lm/W
Warranty period	3 years	Color rendering index (CRI)	>80
Flammability mark	For mounting on normally flammable surfaces	Light source color	840 neutral white
ENEC mark	-	Optic type	Symmetrical
		Optical cover type	Polycarbonate bowl/cover

GreenPerform Highbay Elite

Luminaire light beam spread	90°
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	122 A
Inrush time	0.2 ms
Power Consumption	217 W
Power Factor (Fraction)	0.95
Cable	Cable 0.3 m without plug
Number of products on MCB of 16 A type B 6	
Temperature	
Ambient temperature range	-30 to +50 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Black and gray
Optical cover finish	Frosted
Overall height	464 mm

Overall diameter	510 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.0042 %
Median useful life L70B50	75,000 hour(s)
Application Conditions	
Maximum dim level	1%
Suitable for random switching	No
Product Data	
Order product name	BY718P LED300/NW PSD WB CAU
Full product name	BY718P LED300/NW PSD WB CAU
Full product code	911401581951
Order code	911401581951
Material Nr. (12NC)	911401581951
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



GreenPerform Highbay Elite

