



GreenSpace G5

DN392B LED16/840 PSD D200 WH CAU

GreenSpace G5, 15.5 W, 1600 lm, 4000 K, DALI, High-gloss high reflectance, Matte, Finger-protected

GreenSpace Gen5 is a new LED downlight range combining light efficiency and comfort with product diversity and system compatibility

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light Technical	
Luminous Flux	1,600 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	110 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	92 degree(s)
Light source color	840 neutral white
Optic type	High-gloss high reflectance
Optical cover type	Transparent bowl with white cover

Luminaire light beam spread	80°
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	20.4 A
Inrush time	0.195 ms
Power Consumption	15.5 W
Power Factor (Fraction)	0.95
Cable	Cable with plug
Number of products on MCB of 16 A type B 24	
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

GreenSpace G5

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Black and white
Optical cover finish	Matte
Overall length	0 mm
Overall width	0 mm
Overall height	108 mm
Overall diameter	216 mm
Dimensions (Height x Width x Depth)	108 x 0 x 0 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Initial chromaticity	(0.38,0.38) SDCM<5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.16 %
Median useful life L70B50	50,000 h
Median useful life L80B50	43,000 h
Median useful life L90B50	20,000 h

Product Data

Order product name	DN392B LED16/840 PSD D200 WH CAU
Full product name	DN392B LED16/840 PSD D200 WH CAU
Full product code	911401584741
Order code	911401584741
Material Nr. (12NC)	911401584741
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

