



GreenPerform Highbay G3

BY698X LED160 CW ACW 4 NB

GreenPerform Highbay G3, 120 W, 16000 lm, 6500 K, DALI, 60°

Following the successful introduction of the GreenPerform Highbay G2 in 2013, while continue providing the superior light quality, long service lifetime, reduced energy consumption and less maintenance in the switch on-off (PSU) and Dali dimmable (PSD) versions, the new generation Highbay seamlessly integrates state-of-the-art LED lighting with an easy-to-use and reliable wireless ZIGBEE control solution (ACW) and simple movement detection solution (PIR). In the ACW version products, when the situation on the work floor changes, settings such as dimming levels and timing can be changed wirelessly by the end-users themselves. Luminaires can be combined in groups across the layout, and re-zoning them does not require a hardware change, thus minimising commissioning costs. The system delivers savings over and above the actual efficiency of the LEDs and is future-proof. In the PIR version products, when there has no movement detected after 15 minutes, the lighting will dimming down to 25% of the lumen output, which helps to maximum your energy saving in a simple way. Easy to understand, easy to design-in, and easy to use, GreenPerform Highbay G3 is a smart way to light up your business.

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Service tag	Yes
CE mark	CE mark

3 years
For mounting on normally flammable
surfaces
Temperature 650 °C, duration 5 s
16,000 lm


Datasheet, 2023, May 15 data subject to change

GreenPerform Highbay G3

Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	133 lm/W
Color rendering index (CRI)	>80
Light source color	865 cool daylight
Optic type	Narrow beam
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	60°
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	108 A
Inrush time	0.14 ms
Power Consumption	120 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 3.0 m without plug
Number of products on MCB of 16 A type	10
В	
Temperature	
remperature	
Ambient temperature range	-30 to +45 °C
	-30 to +45 °C
	-30 to +45 °C
Ambient temperature range	-30 to +45 °C Yes
Ambient temperature range Controls and Dimming	
Ambient temperature range Controls and Dimming Dimmable	Yes
Ambient temperature range Controls and Dimming Dimmable Driver/power unit/transformer	Yes Power supply unit with DALI interface
Ambient temperature range Controls and Dimming Dimmable Driver/power unit/transformer Control interface	Yes Power supply unit with DALI interface DALI
Ambient temperature range Controls and Dimming Dimmable Driver/power unit/transformer Control interface	Yes Power supply unit with DALI interface DALI
Ambient temperature range Controls and Dimming Dimmable Driver/power unit/transformer Control interface Constant light output	Yes Power supply unit with DALI interface DALI
Ambient temperature range Controls and Dimming Dimmable Driver/power unit/transformer Control interface Constant light output Mechanical and Housing	Yes Power supply unit with DALI interface DALI No
Ambient temperature range Controls and Dimming Dimmable Driver/power unit/transformer Control interface Constant light output Mechanical and Housing Housing Material	Yes Power supply unit with DALI interface DALI No Aluminum die cast
Ambient temperature range Controls and Dimming Dimmable Driver/power unit/transformer Control interface Constant light output Mechanical and Housing Housing Material Optic material	Yes Power supply unit with DALI interface DALI No Aluminum die cast Polycarbonate

Overall height	105 mm
Overall diameter	417 mm
Approval and Application	
Ingress protection code	IP54 [Dust accumulation-protected, splash-
	proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I
Initial Performance (IEC Complia	nt)
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.313.0.324)SDCM<5
Power consumption tolerance	+/-10%
Over Time Performance (IEC Com	npliant)
Driver failure rate at 5000 h	0.01 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	40,000 hour(s)
Median useful life L90B50	30,000 hour(s)
Application Conditions	
Maximum dim level	10%
Suitable for random switching	Yes
Product Data	
Order product name	BY698X LED160 CW ACW 4 NB
Full product name	BY698X LED160 CW ACW 4 NB
Full product code	911401595631
Order code	911401595631
Material Nr. (12NC)	911401595631
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing





GreenPerform Highbay G3



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.