

Tango G3 - BVP38x

BVP383 LED408/NW 310W 220-240V SWB ANZ

Tango G3 - BVP38x, 40800 lm, 310 W, 740 neutral white, Safety class I

The energy-saving Philips Tango G3 LED Floodlight is the ideal solution for a wide range of Area lighting applications. It incorporates the LED light source, optical system, heat sink and driver into one compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, this luminaire delivers superior performance and a longer lifetime, bringing area lighting to a whole new level.

Product data

General Information	
Driver included	Yes
Lighting Technology	LED
CE mark	CE mark

Light Technical	
Luminous Flux	40,800 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	134 lm/W
Color rendering index (CRI)	>70
Light source color	740 neutral white
Optical cover type	Polycarbonate micro lens optic

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	310 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Cable	Cable 0.5 m without plug

Temperature	
Ambient temperature range	-40 to +50 °C

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Polycarbonate

Tango G3 - BVP38x

Housing Color	Aluminum and gray

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP383 LED408/NW 310W 220-240V SWB ANZ
Full product name	BVP383 LED408/NW 310W 220-240V SWB ANZ
Full product code	911401604506
Order code	911401604506
Material Nr. (12NC)	911401604506
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.