



# Tango G3 - BVP38x

## BVP383 LED360/NW 320W 220-240V SWB ANZ

Tango G3 - BVP38x, 36000 lm, 320 W, Neutral white, Symmetrical wide beam, 30° x 80°, Safety class I, Mounting bracket adjustable

The energy-saving Philips Tango G3 LED Floodlight is the ideal solution for a wide range of Area lighting applications. It incorporates the LED light source, optical system, heat sink and driver into one compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, this luminaire delivers superior performance and a longer lifetime, bringing area lighting to a whole new level.

### Product data

General Information		Standard tilt angle side entry	
Lamp family code	-	Correlated Color Temperature (Nom)	4000 K
Light source replaceable	Yes	Luminous Efficacy (rated) (Nom)	110 lm/W
Driver included	Yes	Color rendering index (CRI)	>70
Light source engine type	LED	Light source color	Neutral white
Lighting Technology	LED	Optical cover type	Polycarbonate micro lens optic
CE mark	CE mark	Luminaire light beam spread	30° x 80°
Warranty period	3 years	Optic type outdoor	Symmetrical wide beam
Flammability mark	-		
ENEC mark	-	Operating and Electrical	
EU RoHS compliant	No	Input Voltage	220-240 V
		Line Frequency	50 or 60 Hz
		Inrush current	138 A
		Inrush time	0.44 ms
		Power Consumption	320 W
Light Technical			
Luminous Flux	36,000 lm		
Standard tilt angle posttop	-		

## Tango G3 - BVP38x

Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug
Number of products on MCB of 16 A type B	2

### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-

### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover shape	-
Optical cover finish	Frosted
Overall length	591 mm
Overall width	114 mm
Overall height	603 mm
Effective projected area	0.29 m <sup>2</sup>

Dimensions (Height x Width x Depth)	603 x 114 x 591 mm
-------------------------------------	--------------------

### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM < 7
Power consumption tolerance	+/-10%

### Product Data

Order product name	BVP383 LED360/NW 320W 220-240V SWB ANZ
Full product name	BVP383 LED360/NW 320W 220-240V SWB ANZ
Full product code	911401611604
Local code description	BVP3833604KSWB
Order code	911401611604
Material Nr. (12NC)	911401611604
Local order code	BVP3833604KSWB
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

