



# UNiStrip G2 RGB

## BCP280 G2 9xLED-HP/RGB 24V L313 NB

UNiStrip G2 is a LED lighting fixture designed for wide range architecture wall washer lighting applications. UNiStrip G2 offers reliable quality and outstanding performance

### Product data

General Information	
Lamp colour code	Red, green and blue (RGB)
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	ET [ Electronic transformer]
Driver included	No
Optical cover/lens type	PC-S [ Polycarbonate small]
Control interface	Dynamix DMX
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug (C1K5)
Protection class IEC	Safety class III (III)
Flammability mark	F [ For mounting on normally flammable surfaces]
CE mark	CE mark
ENEC mark	-
Warranty period	3 years
Constant light output	No
LED engine type	LED
Light Technical	
Standard tilt angle post-top	-
Standard tilt angle side entry	-
Operating and Electrical	
Input voltage	24 DC V

Power factor (min.)	0.95
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing material	Aluminum extruded
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminium
Mounting device	MBA [ Mounting bracket adjustable]
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	313 mm
Overall width	63 mm
Overall height	59 mm
Colour	Aluminum and black
Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [ 1 J]
Initial Performance (IEC Compliant)	
Initial luminous flux	570 lm
Luminous flux tolerance	+/-10%


# UNiStrip G2 RGB

Initial LED luminaire efficacy	44 lm/W
Lamp colour temperature	- K
Colour Rendering Index	-
Initial input power	13 W
Power consumption tolerance	+/-15%


<b>Application Conditions</b>	
Ambient temperature range	-40 to +50 °C
Maximum dimming level	0% (digital)

<b>Product Data</b>	
Full product code	911401621003

Order product name	BCP280 G2 9xLED-HP/RGB 24V L313 NB
Order code	911401621003
Numerator – quantity per pack	1
Numerator – packs per outer box	8
Material no. (12NC)	911401621003
Net weight (piece)	0.899 kg



## Dimensional drawing



### BCP280 UNiStrip G2

