



UNIstrip G2 RGB

BCP280 G2 9xLED-HP/RGB 24V L313 NB

UNIstrip G2 RGB, 570 lm, 13 W, Red, green and blue, Dynamix DMX, Safety class III, Mounting bracket adjustable

UNIstrip G2 is a LED lighting fixture designed for wide range architecture wall washer lighting applications. UNIstrip G2 offers reliable quality and outstanding performance

Product data

General Information		Optical cover type	
Light source replaceable	No	Polycarbonate small	
Number of gear units	1 unit	Operating and Electrical	
Driver included	No	Input Voltage	24 DC V
Light source engine type	LED	Power Consumption	13 W
Lighting Technology	LED	Power Factor (Fraction)	0.95
CE mark	CE mark	Connection	Flying leads/wires
Warranty period	3 years	Cable	Cable 1.5 m without plug
Flammability mark	For mounting on normally flammable surfaces	Temperature	
ENEC mark	-	Ambient temperature range	-40 to +50 °C
EU RoHS compliant	Yes	Controls and Dimming	
Light Technical		Dimmable	Yes
Luminous Flux	570 lm	Driver/power unit/transformer	Electronic transformer
Standard tilt angle posttop	-	Control interface	Dynamix DMX
Standard tilt angle side entry	-	Constant light output	No
Correlated Color Temperature (Nom)	-	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	44 lm/W	Housing Material	Aluminum extruded
Color rendering index (CRI)	-	Optic material	Polycarbonate
Light source color	Red, green and blue		

UNIstrip G2 RGB

Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Aluminum and black
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	313 mm
Overall width	63 mm
Overall height	59 mm
Dimensions (Height x Width x Depth)	59 x 63 x 313 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class III

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-15%
-----------------------------	--------

Application Conditions

Maximum dim level	0% (digital)
-------------------	--------------

Product Data

Order product name	BCP280 G2 9xLED-HP/RGB 24V L313 NB
Full product name	BCP280 G2 9xLED-HP/RGB 24V L313 NB
Full product code	911401621003
Order code	911401621003
Material Nr. (12NC)	911401621003
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8

Dimensional drawing

