



UNiStrip G2 RGB

BCP280 G2 36xLED-HP/RGB 24V L1190 NB

UNiStrip G2 is a LED lighting fixture designed for wide range architecture wall washer lighting applications. UNiStrip G2 offers reliable quality and outstanding performance

Product data

General Information	
Lamp colour code	Red, green and blue (RGB)
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	ET [Electronic transformer]
Driver included	No
Optical cover/lens type	PC-S [Polycarbonate small]
Control interface	Dynamix DMX
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug (C1K5)
Protection class IEC	Safety class III (III)
Flammability mark	F [For mounting on normally flammable surfaces]
CE mark	CE mark
ENEC mark	-
Warranty period	3 years
Constant light output	No
LED engine type	LED
Light Technical	
Standard tilt angle post-top	-
Standard tilt angle side entry	-
Operating and Electrical	
Input voltage	24 DC V

Power factor (min.)	0.95
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing material	Aluminum extruded
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminium
Mounting device	MBA [Mounting bracket adjustable]
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	1190 mm
Overall width	63 mm
Overall height	59 mm
Colour	Aluminum and black
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Initial Performance (IEC Compliant)	
Initial luminous flux	2280 lm
Luminous flux tolerance	+/-10%


UNISTrip G2 RGB

Initial LED luminaire efficacy	45 lm/W
Lamp colour temperature	- K
Colour Rendering Index	-
Initial input power	51 W
Power consumption tolerance	+/-15%


Application Conditions	
Ambient temperature range	-40 to +50 °C
Maximum dimming level	0% (digital)

Product Data	
Full product code	911401621203

Order product name	BCP280 G2 36xLED-HP/RGB 24V L1190 NB
Order code	911401621203
Numerator – quantity per pack	1
Numerator – packs per outer box	4
Material no. (12NC)	911401621203
Net weight (piece)	2.499 kg



Dimensional drawing



BCP280 UNISTrip G2

