



# RoadFlair

## BRP392 LED144/NW 120W 220-240V DM MP1

RoadFlair, 14400 lm, 120 W, 740 neutral white, Medium beam, Safety class I, Side-entry for diameter 48 to 60 mm

Designed for major and city roads, Philips RoadFlair is a new and exciting product set to brighten your streets beyond imagination. Smartly-designed to bring cities the highest savings possible with best-in-class lumen per watt, this road lighting production comes at a competitive price bound to excite. Philips RoadFlair brings energy efficiency, improves a city's sustainability drive and delivers significant cost reduction in urban environments. The right road luminaire coupled with the right lighting application will create the best environment for your municipality, benefiting local communities and boosting tourism and businesses.

### Product data

General Information		Optic type outdoor	
Light source replaceable	No	Medium beam	
Driver included	Yes	Operating and Electrical	
Light source engine type	LED	Input Voltage	220-240 V
CE mark	CE mark	Line Frequency	50 or 60 Hz
Flammability mark	For mounting on normally flammable surfaces	Power Consumption	120 W
Light Technical		Power Factor (Fraction)	0.95
Luminous Flux	14,400 lm	Connection	Mains outlet socket
Standard tilt angle side entry	5°	Cable	Cable 0.5 m without plug
Correlated Color Temperature (Nom)	4000 K	Temperature	
Luminous Efficacy (rated) (Nom)	120 lm/W	Ambient temperature range	-30 to +50 °C
Color rendering index (CRI)	>70	Controls and Dimming	
Light source color	740 neutral white	Dimmable	No
Optical cover type	Polycarbonate micro lens optic		

## RoadFlair

Control interface	-
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Grey
Mounting device	Side-entry for diameter 48 to 60 mm
Optical cover shape	Ball, globular
Overall length	492 mm
Overall width	295 mm
Overall height	86 mm
Effective projected area	0.14 m <sup>2</sup>
Dimensions (Height x Width x Depth)	86 x 295 x 492 mm

### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
-------------------------	--

Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
Initial chromaticity	(0.43, 0.40) SDCM < 5
Power consumption tolerance	+/-5%

### Product Data

Order product name	BRP392 LED144/NW 120W 220-240V DM MP1
Full product name	BRP392 LED144/NW 120W 220-240V DM MP1
Full product code	911401622403
Order code	911401622403
Material Nr. (12NC)	911401622403
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

### Dimensional drawing

