PHILIPS Lighting



Smart Post-top G3

BGP161 LED2500/NW PSU 220-240V 7043 IN

Smart Post-top G3, 2500 lm, 29 W, Neutral white, Symmetrical, Safety class I, Post-top for diameter 60 mm

Smart Post Top G3 inherits the classic look and style of the previous generation with improved system efficacy and light quality. The Smart Post Top G3 optimized optical design increases both horizontal and vertical uniformity. The highly efficient thermal system design ensures maximum heat transfer and longer LED service life. This reliable luminaire system operates well in both low and high temperature environments. It offers more than 11 years expected life, reducing maintenance frequency and cost (based on a 50,000 hour rated life and 12 hours operation per day). It provides a comfortable and safe atmosphere to gardens, residential areas, courtyards, side streets, squares, parks & playgrounds.


Product data

al Information		Luminous Flux	2,500 lm
o family code	-	Standard tilt angle posttop	-
ht source replaceable	Yes	Standard tilt angle side entry	-
mber of gear units	1 unit	Correlated Color Temperature (Nom)	4000 K
river included	Yes	Luminous Efficacy (rated) (Nom)	86.21 lm/W
ight source engine type	LED	Color rendering index (CRI)	70
E mark	-	Light source color	Neutral white
Varranty period	3 years	Optical cover type	Acrylate cover and semi-matt hig
ammability mark	-		reflective optic
NEC mark	-	Luminaire light beam spread	-
U RoHS compliant	Yes	Optic type outdoor	Symmetrical
ight Technical		Operating and Electrical	
Upward light output ratio	0	Input Voltage	220 to 240 V

Smart Post-top G3

Line Frequency	50 to 60 Hz	Overall diameter	578 mm
Inrush current	2.1 A		
Inrush time	22.3 ms	Approval and Application	
Power Consumption	29 W	Ingress protection code	IP65 [Dust penetration-protected, jet-proc
Power Factor (Fraction)	0.9	Mech. impact protection code	IK07 [2 J reinforced]
Connection	Flying leads/wires	Surge Protection (Common/Differential)	4/2 kV
Cable	Cable 0.45 m without plug	Protection class IEC	Safety class I
Number of products on MCB of 16 A	type B -		
		Initial Performance (IEC Compliant)	
Temperature		Luminous flux tolerance	+/-10%
Ambient temperature range	-40 to +50 °C	Initial chromaticity	SDCM>5
		Power consumption tolerance	+/-10%
Controls and Dimming			
Dimmable	No	Application Conditions	
Driver/power unit/transformer	Power supply unit (On/Off)	Maximum dim level	Not applicable
Control interface	-		
Constant light output	No	Product Data	
		Order product name	BGP161 LED2500/NW PSU 220-240V 704
Mechanical and Housing			IN
Housing Material	Aluminum die cast	Full product name	BGP161 LED2500/NW PSU 220-240V 704
Reflector material	Acrylate		IN
Optic material	Acrylate	Full product code	911401633703
Optical cover material	Acrylate	Order code	911401633703
Fixation material	Stainless steel	Material Nr. (12NC)	911401633703
Housing Color	Dark gray	Numerator - Quantity Per Pack	1
Mounting device	Post-top for diameter 60 mm	Numerator - Packs per outer box	2
Optical cover shape	Flat		
Optical cover finish	Frosted		
Overall height	265 mm		

Dimensional drawing



Smart Post-top G3



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 14 - data subject to change