



# **Smart Post-top G3**

#### BGP161 LED2300/WW PSU 220-240V 7043 IN

Smart Post-top G3, 2300 lm, 27 W, Warm white, Symmetrical, Safety class I, Post-top for diameter 60 mm

Smart Post Top G3 inherits the classic look and style of the previous generation with improved system efficacy and light quality. The Smart Post Top G3 optimized optical design increases both horizontal and vertical uniformity. The highly efficient thermal system design ensures maximum heat transfer and longer LED service life. This reliable luminaire system operates well in both low and high temperature environments. It offers more than 11 years expected life, reducing maintenance frequency and cost (based on a 50,000 hour rated life and 12 hours operation per day). It provides a comfortable and safe atmosphere to gardens, residential areas, courtyards, side streets, squares, parks & playgrounds.

#### **Product data**

General Information	
Lamp family code	-
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	-
Warranty period	3 years
Warranty period Flammability mark	3 years
	3 years -
Flammability mark	-
Flammability mark ENEC mark	-
Flammability mark ENEC mark	-
Flammability mark  ENEC mark  EU RoHS compliant	-

Luminous Flux	2,300 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	85.19 lm/W
Color rendering index (CRI)	70
Light source color	Warm white
Optical cover type	Acrylate cover and semi-matt high-
	reflective optic
Luminaire light beam spread	-
Optic type outdoor	Symmetrical
Operating and Electrical	
Input Voltage	220 to 240 V


Datasheet, 2023, April 14 data subject to change

## **Smart Post-top G3**

Line Frequency	50 to 60 Hz	
Inrush current	2.1 A	
Inrush time	22.3 ms	
Power Consumption	27 W	
Power Factor (Fraction)	0.9	
Connection	Flying leads/wires	
Cable	Cable 0.45 m without plug	
Number of products on MCB of 16 A type B -		
Temperature		
Ambient temperature range	-40 to +50 °C	
Controls and Dimming		
Dimmable	No	
Driver/power unit/transformer	Power supply unit (On/Off)	
Control interface	-	
Constant light output	No	
Mechanical and Housing		
Housing Material	Aluminum die cast	
Reflector material	Acrylate	
Optic material	Acrylate	
Optical cover material	Acrylate	
Fixation material	Stainless steel	
Housing Color	Dark gray	
Mounting device	Post-top for diameter 60 mm	
Optical cover shape	Flat	
Optical cover finish	Frosted	
Overall height	265 mm	

Overall diameter	578 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Surge Protection (Common/Differential)	4/2 kV
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM>5
Power consumption tolerance	+/-10%
<b>Application Conditions</b>	
Maximum dim level	Not applicable
Product Data	
Order product name	BGP161 LED2300/WW PSU 220-240V 7043
	IN
Full product name	BGP161 LED2300/WW PSU 220-240V 7043
	IN
Full product code	911401633903
Order code	911401633903
Material Nr. (12NC)	911401633903
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

#### Dimensional drawing



## **Smart Post-top G3**



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.