PHILIPS Lighting



CoreLine Downlight

DN140B LED20S/830 C IA1

CoreLine Downlight, 22 W, D200 mm, 2200 lm, 3000 K, Wireless, Interact Ready, High-gloss reflector, Frosted, IP20

The CoreLine Downlight range of recessed luminaires is designed to replace CFLni/CFL-i based downlight luminaires. Their attractive TCO helps customers to make the switch to LED.These luminaires create a natural lighting effect for use in general lighting applications. They also deliver instant energy savings and have a much longer lifetime, creating a real value-for-money and environmentally friendly solution. They are easy to install thanks to their standard cut-out size and push-in connectors.

Product data

General Information		
Light source replaceable	No	
Number of gear units	Unit	
Driver included	Yes	
Remarks	*- According to the Lighting Europe	
	guidance paper 'Evaluating performance of	
	LED based luminaires – January 2018':	
	statistically there is no relevant difference in	
	lumen maintenance between the B50 and,	
	for example, the B10. Therefore, the median	
	useful life (B50) value also represents the	
	B10 value.	
Product family code	DN140B [Coreline Downlight Gen4]	
Connectivity	Interact Ready	
Lighting Technology	LED	
Value ladder	Performance	
Embedded control	Interact SNS210 sensor	

CE mark	Yes	
Warranty period	5 years	
Flammability mark	For mounting on normally flammable	
	surfaces	
ENEC mark	-	
Glow-wire test	Temperature 850 °C, duration 5 s	
EU RoHS compliant	Yes	
Light Technical		
Luminous Flux	2,200 lm	
Correlated Colour Temperature	3000 K	
Luminous efficacy (rated) (nom.)	100 lm/W	
Colour rendering index (CRI)	≥80	
Beam angle of light source	120 degree(s)	
Light source colour	830 warm white	
Optic type	-	

CoreLine Downlight

Luminaire light beam spread	60°	Overall height	108 mm
Unified Glare Rating (CEN)	22	Overall diameter	216 mm
		Dimensions (height x width x depth)	108 x 0 x 0 mm
Operating and Electrical			
Input Voltage	220-240 V	Approval and Application	
Line Frequency	50 to 60 Hz	Ingress protection code	IP20 [Finger-protected]
Initial CLO power consumption	- W W	Mech. impact protection code	IK02 [0.2 J standard]
Average CLO power consumption	- W W	Protection class IEC	Safety class I
End CLO power consumption	- W		
Inrush current	12 A	Initial Performance (IEC Compliant)	
Inrush time	0.25 ms	Luminous flux tolerance	+/-10%
Power Consumption	22 W	Initial chromaticity	(0.432,0.404) SDCM≦5
Power Factor (Fraction)	0.9	Power consumption tolerance	+/-10%
Connection	Push-in connector and pull relief		
Cable	-	Over Time Performance (IEC Compliant)	
Number of products on MCB of 16 A ty	уре В 24	Driver failure rate at 5,000 hours	1%
		Control gear failure rate at median useful	5 %
Temperature		life 50,000 h	
Ambient temperature range	-20 to +40 ℃	Lumen maintenance at median useful life*	L70
		50,000 h	
Controls and Dimming			
Dimmable	Yes	Application Conditions	
Driver/power unit/transformer	Power supply unit with SystemReady	Performance ambient temperature Tq	25 ℃
	interface, Interact-ready	Maximum dim level	1%
Control interface	Wireless	Suitable for random switching	Yes
Constant light output	No		
		Product Data	
Mechanical and Housing		Order product name	DN140B LED20S/830 C IA1
Housing material	Polycarbonate	Full product name	DN140B LED20S/830 C IA1
Reflector material	Aluminium and polycarbonate	Full EOC	871016332614600
Optic material	Polycarbonate	Order code	32614600
Optical cover/lens material	Polycarbonate	Material no. (12 NC)	911401634405
Fixation material	Steel	SAP numerator - quantity per pack	1
Housing Colour	White	EAN/UPC — Product/Case	8710163326146
Optical cover/lens finish	Frosted	Numerator – packs per outer box	1
Reflector finish	High-gloss reflector	EAN/UPC - Case	8710163326146
Overall length	0 mm		
Overall width	0 mm	_	

Dimensional drawing



CoreLine Downlight



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 29 - data subject to change