



RoadCharm

BRP472 LED 293/NW 228W 220-240V DME

Developed with the aim to become your long term partner ,the system ready architecture of RoadCharm enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come. ;It is designed to achieve better light uniformity and maximum spacing between poles for both pedestrian and vehicle road applications. With its die-cast aluminum housing and Philips LED platform, it is easy to maintain, has a long lifetime and a consistency you can count on. It also offers 2 housing sizes and a range of beam optics to fully cater to different road configurations and conditions. ;RoadCharm offers 50% energy savings compared to conventional lamp systems, making it the perfect sustainable lighting solution for any emerging metropolis.

Product data

General Information		control units, surge protection device, front cover and mechanical parts	
Light source color	740 neutral white		
Light source replaceable	No		
Driver included	Yes		
Optical cover/lens type	PC-MLO [Polycarbonate micro lens optic]		
Control interface	-		
Connection	Mains outlet socket		
Cable	-		
Protection class IEC	Safety class I (I)		
Flammability mark	NO [-]		
CE mark	CE mark		
ENEC mark	-		
Constant light output	No		
Light source engine type	LED		
Serviceability class	Class B, luminaire is equipped with some serviceable parts (when applicable): driver,		
Light Technical		Operating and Electrical	
Standard tilt angle posttop	-	Input Voltage	220 to 240 V
		Input Frequency	50 or 60 Hz
		Power Factor (Min)	0.9
Controls and Dimming		Mechanical and Housing	
Dimmable	No	Housing Material	Aluminum die-cast
		Optic material	Polycarbonate

RoadCharm

Optical cover/lens material	Polycarbonate
Mounting device	48/60S [Side-entry for diameter 48-60 mm]
Optical cover/lens shape	Ball, globular
Optical cover/lens finish	Clear
Overall length	1012 mm
Overall width	364 mm
Overall height	115 mm
Effective projected area	0.32 m ²
Color	Gray

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	29300 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	130 lm/W


Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	>70
Initial input power	228 W
Power consumption tolerance	+/-10%

Application Conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product Data

Full product code	911401662105
Order product name	BRP472 LED 293/NW 228W 220-240V DME
Order code	911401662105
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	911401662105
Net Weight (Piece)	13.799 kg



Dimensional drawing



BRP47X

