



Tango G2 LED

BVP282 LED202/NW 160W 220-240V SMB

Tango G2 LED, 20200 lm, 160 W, Neutral white, Symmetrical medium beam, 54°, Safety class I, Mounting bracket adjustable

Tango G2 LED is a general purpose LED flood lighting luminaire for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.

Product data

| | | | | |
|-----------------------------|-----------|---------------------------------------|--------------------------------|---|
| General Information | | Standard tilt angle side entry | | - |
| Lamp family code | - | Correlated Color Temperature (Nom) | 4000 K | |
| Light source replaceable | Yes | Luminous Efficacy (rated) (Nom) | 125 lm/W | |
| Number of gear units | - | Color rendering index (CRI) | 70 | |
| Driver included | Yes | Light source color | Neutral white | |
| Light source engine type | LED | Optical cover type | Polycarbonate micro lens optic | |
| Lighting Technology | LED | Luminaire light beam spread | 54° | |
| CE mark | CE mark | Optic type outdoor | Symmetrical medium beam | |
| Warranty period | 3 years | Operating and Electrical | | |
| Flammability mark | - | Input Voltage | 220-240 V | |
| ENEC mark | - | Line Frequency | 50 or 60 Hz | |
| EU RoHS compliant | No | Initial CLO power consumption | - W | |
| Light Technical | | Average CLO power consumption | - W | |
| Luminous Flux | 20,200 lm | End CLO power consumption | - W | |
| Standard tilt angle posttop | - | Power Consumption | 160 W | |

Tango G2 LED

| | |
|--|--------------------------|
| Power Factor (Fraction) | 0.95 |
| Connection | Flying leads/wires |
| Cable | Cable 1.5 m without plug |
| Number of products on MCB of 16 A type B - | |

Temperature

| | |
|---------------------------|---------------|
| Ambient temperature range | -40 to +50 °C |
|---------------------------|---------------|

Controls and Dimming

| | |
|-------------------------------|----------------------------|
| Dimmable | No |
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Control interface | - |
| Constant light output | No |

Mechanical and Housing

| | |
|------------------------|-----------------------------|
| Housing Material | Aluminum die cast |
| Reflector material | - |
| Optic material | Polycarbonate |
| Optical cover material | Polycarbonate |
| Fixation material | Steel |
| Housing Color | Aluminum and gray |
| Mounting device | Mounting bracket adjustable |
| Optical cover shape | - |
| Optical cover finish | Frosted |
| Overall length | 655 mm |
| Overall width | 480 mm |
| Overall height | 60 mm |

| | |
|-------------------------------------|-------------------|
| Effective projected area | 0.25 m² |
| Dimensions (Height x Width x Depth) | 60 x 480 x 655 mm |

Approval and Application

| | |
|--|--|
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK07 [2 J reinforced] |
| Surge Protection (Common/Differential) | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| Protection class IEC | Safety class I |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|---------|
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | SDCM<=7 |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|---------------------------------|------------------------------------|
| Order product name | BVP282 LED202/NW 160W 220-240V SMB |
| Full product name | BVP282 LED202/NW 160W 220-240V SMB |
| Full product code | 872016973001400 |
| Order code | 911401663604 |
| Material Nr. (12NC) | 911401663604 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169730014 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8720169730014 |

Dimensional drawing



Tango G2 LED

