
PHILIPS Lighting



Tango G2 LED

BVP282 LED202/CW 160W 220-240V SWB

Tango G2 LED, 20200 lm, 160 W, Cool white, Symmetrical wide beam, 100°, Safety class I, Mounting bracket adjustable

Tango G2 LED is a general purpose LED flood lighting luminiare for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.

Product data


| General Information | |
|-----------------------------|-----------|
| Lamp family code | - |
| Light source replaceable | Yes |
| Number of gear units | - |
| Driver included | Yes |
| Light source engine type | LED |
| Lighting Technology | LED |
| CE mark | CE mark |
| Warranty period | 3 years |
| Flammability mark | - |
| ENEC mark | - |
| EU RoHS compliant | No |
| | |
| Light Technical | |
| Luminous Flux | 20,200 lm |
| Standard tilt angle posttop | - |

| Standard tilt angle side entry | - | |
|------------------------------------|--------------------------------|--|
| Correlated Color Temperature (Nom) | 5700 K | |
| Luminous Efficacy (rated) (Nom) | 125 lm/W | |
| Color rendering index (CRI) | 70 | |
| Light source color | Cool white | |
| Optical cover type | Polycarbonate micro lens optic | |
| Luminaire light beam spread | 100° | |
| Optic type outdoor | Symmetrical wide beam | |
| | | |
| Operating and Electrical | | |
| Input Voltage | 220-240 V | |
| Line Frequency | 50 or 60 Hz | |
| Initial CLO power consumption | - W | |
| Average CLO power consumption | - W | |
| End CLO power consumption | - W | |
| Power Consumption | 160 W | |
| | | |

Tango G2 LED

| Power Factor (Fraction) | 0.95 | Effective projected area | 0.25 m² |
|--|-----------------------------|--|--|
| Connection | Flying leads/wires | Dimensions (Height x Width x Depth) | 60 x 480 x 655 mm |
| Cable | Cable 1.5 m without plug | | |
| Number of products on MCB of 16 A type B - | | Approval and Application | |
| | | Ingress protection code | IP65 [Dust penetration-protected, jet-proo |
| Temperature | | Mech. impact protection code | IK07 [2 J reinforced] |
| Ambient temperature range | -40 to +50 °C | Surge Protection (Common/Differential) | Luminaire surge protection level until 10 kV |
| | | | differential mode and 10 kV common mode |
| Controls and Dimming | | Protection class IEC | Safety class I |
| Dimmable | No | | |
| Driver/power unit/transformer | Power supply unit (On/Off) | Initial Performance (IEC Compliant) | |
| Control interface | - | Luminous flux tolerance | +/-10% |
| Constant light output | No | Initial chromaticity | SDCM<=7 |
| | | Power consumption tolerance | +/-10% |
| Mechanical and Housing | | | |
| Housing Material | Aluminum die cast | Product Data | |
| Reflector material | - | Order product name | BVP282 LED202/CW 160W 220-240V SWE |
| Optic material | Polycarbonate | Full product name | BVP282 LED202/CW 160W 220-240V SWE |
| Optical cover material | Polycarbonate | Full product code | 872016972979700 |
| Fixation material | Steel | Order code | 911401663704 |
| Housing Color | Aluminum and gray | Material Nr. (12NC) | 911401663704 |
| Mounting device | Mounting bracket adjustable | Numerator - Quantity Per Pack | 1 |
| Optical cover shape | - | EAN/UPC - Product/Case | 8720169729797 |
| Optical cover finish | Frosted | Numerator - Packs per outer box | 1 |
| Overall length | 655 mm | EAN/UPC - Case | 8720169729797 |
| Overall width | 480 mm | | |
| Overall height | 60 mm | | |
| | | | |

Dimensional drawing



Tango G2 LED



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 29 - data subject to change