


Tango G2 LED

BVP282 LED202/WW 160W 220-240V SMB

Tango G2 LED, 20200 lm, 160 W, Warm white, Symmetrical medium beam, 54°, Safety class I, Mounting bracket adjustable

Tango G2 LED is a general purpose LED flood lighting luminiare for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.

Product data

General Information	
Lamp family code	-
Light source replaceable	Yes
Number of gear units	-
Driver included	Yes
Light source engine type	LED
Lighting Technology	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	-
ENEC mark	-
EU RoHS compliant	No

Light Technical	
Luminous Flux	20,200 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	125 lm/W
Color rendering index (CRI)	70
Light source color	Warm white
Optical cover type	Polycarbonate micro lens optic
Luminaire light beam spread	54°
Optic type outdoor	Symmetrical medium beam

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
End CLO power consumption	- W
Power Consumption	160 W

Tango G2 LED

Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug
Number of products on MCB of 16 A type B	-

Temperature

Ambient temperature range	-40 to +50 °C

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover shape	-
Optical cover finish	Frosted
Overall length	655 mm
Overall width	480 mm
Overall height	60 mm

Effective projected area	0.25 m²
Dimensions (Height x Width x Depth)	60 x 480 x 655 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class I


Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<=7
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP282 LED202/WW 160W 220-240V SMB
Full product name	BVP282 LED202/WW 160W 220-240V SMB
Full product code	872016972986500
Order code	911401664704
Material Nr. (12NC)	911401664704
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169729865
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169729865

Dimensional drawing



Tango G2 LED

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com
2023, May 16 - data subject to change