



SmartBright LED Floodlight

BVP174 LED95/WW 100W WB GREY SAA KC

SmartBright LED Floodlight, 9500 lm, 100 W, 730 warm white, 30° x 80°, Safety class I, Mounting bracket adjustable

The SmartBright LED Floodlight is a versatile floodlight engineered to deliver significant energy savings, an ideal solution for diverse floodlighting applications. The product is also designed to meet relevant performance and safety standards, offering you reliable and long-lasting performance.

Product data

General Information		Luminaire light beam spread	
Lamp family code	LED66 [LED module 6600 lm]	30° x 80°	
Light source replaceable	No	Operating and Electrical	
Driver included	Yes	Input Voltage	220 to 240 V
Light source engine type	LED	Line Frequency	50 or 60 Hz
Lighting Technology	LED	Inrush current	9.7 A
CE mark	CE mark	Inrush time	0.065 ms
Flammability mark	For mounting on normally flammable surfaces	Power Consumption	100 W
		Power Factor (Fraction)	0.9
		Connection	Flying leads/wires
		Cable	Cable 0.6 m without plug
		Number of products on MCB of 16 A type B 26	
Light Technical		Temperature	
Luminous Flux	9,500 lm	Ambient temperature range	
Correlated Color Temperature (Nom)	3000 K	-40 to +45 °C	
Luminous Efficacy (rated) (Nom)	95 lm/W		
Color rendering index (CRI)	>70		
Light source color	730 warm white		
Optical cover type	Polycarbonate bowl/cover UV-resistant		

SmartBright LED Floodlight

Controls and Dimming	
Dimmable	No
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Polycarbonate
Housing Color	Grey
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Frosted
Overall length	356 mm
Overall width	190 mm
Overall height	53 mm
Effective projected area	0.11036 m²
Dimensions (Height x Width x Depth)	53 x 190 x 356 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<7
Power consumption tolerance	+/-10%
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	BVP174 LED95/WW 100W WB GREY SAA KC
Full product name	BVP174 LED95/WW 100W WB GREY SAA KC
Full product code	871016332102899
Order code	911401690804
Material Nr. (12NC)	911401690804
Local order code	BVP174WW100W
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163321028
Numerator - Packs per outer box	6
EAN/UPC - Case	8710163321622

Dimensional drawing

