



# UniPoint

## BGP312 3LED 2700K WB GG

Our UniPoint is designed to produce both general and accent lighting while concealing the body of the device, allowing only the light to be exposed. This design can be used to change the surroundings by adding subtle or dramatic contrasting effects. It also includes exclusive features such as energy efficiency, chromatic quality and miniaturisation. We guarantee extreme reliability and high level of resistance to adverse weather conditions and vandalism

### Product data

General Information	
Light source colour	827 warm white
Light source replaceable	No
Driver/power unit/transformer	ET [ Electronic transformer]
Driver included	No
Optical cover/lens type	GB [ Glass bowl/cover]
Luminaire light beam spread	40°
Control interface	-
Connection	Flying leads/wires
Cable	Cable without plug 2-pole
Protection class IEC	Safety class III (III)
CE mark	CE mark
Warranty period	3 years
Outdoor optic type	Wide beam angle 42°
Constant light output	No
LED engine type	LED
Light Technical	
Standard tilt angle post-top	-
Standard tilt angle side entry	-

Operating and Electrical	
Input voltage	24 DC V
Input frequency	45 to 66 Hz
Inrush current	0.7 A
Inrush time	10 ms
Power factor (min.)	0.97
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing material	Aluminum die-cast
Reflector material	Glass
Optical cover/lens material	Glass
Mounting device	Allen screw fixation
Optical cover/lens shape	Conical
Optical cover/lens finish	Textured
Overall length	95.8 mm
Overall height	69.4 mm
Overall diameter	65.5 mm

Colour	Dark gray
<b>Approval and Application</b>	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [ 1 J]
<b>Initial Performance (IEC Compliant)</b>	
Initial luminous flux	330 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	55 lm/W
Init. Corr. colour temperature	2700 K
Init. colour rendering index	>75
Initial chromaticity	SDCM<5
Initial input power	6 W
Power consumption tolerance	+/-10%

## Application Conditions


Ambient temperature range	-40 to +45 °C
---------------------------	---------------

## Product Data

Full product code	911401711552
Order product name	BGP312 3LED 2700K WB GG
Order code	01711552
Numerator – quantity per pack	1
Numerator – packs per outer box	32
Material no. (12NC)	911401711552
Net weight (piece)	0.399 kg



## Dimensional drawing



BGP312 UniPoint

