



# **UniPoint**

## **BGP312 5LED 3000K NB GG**

UniPoint, 595 lm, 10 W, 830 warm white, Narrow beam angle 10°, 10°, Safety class III, Allen screw fixation

Our UniPoint is designed to produce both general and accent lighting while concealing the body of the device, allowing only the light to be exposed. This design can be used to change the surroundings by adding subtle or dramatic contrasting effects. It also includes exclusive features such as energy efficiency, chromatic quality and miniaturization. We guarantee extreme reliability and high level of resistance to adverse weather conditions and vandalism

#### **Product data**

General Information	
Light source replaceable	No
Driver included	No
Light source engine type	LED
Lighting Technology	LED
CE mark	CE mark
Warranty period	3 years
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	595 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	59 lm/W
Color rendering index (CRI)	>75
Light source color	830 warm white
	·

Optical cover type	Glass bowl/cover
Luminaire light beam spread	10°
Optic type outdoor	Narrow beam angle 10°
Operating and Electrical	
Input Voltage	24 DC V
Line Frequency	45 to 66 Hz
Inrush current	1A
Inrush time	10 ms
Power Consumption	10 W
Power Factor (Fraction)	0.97
Connection	Flying leads/wires
Cable	Cable without plug 2-pole
Temperature	
Ambient temperature range	-40 to +45 °C

Datasheet, 2023, November 21 data subject to change

# **UniPoint**

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Electronic transformer
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	Glass
Optical cover material	Glass
Housing Color	Dark gray
Mounting device	Allen screw fixation
Optical cover shape	Conical
Optical cover finish	Textured
Overall length	123.5 mm
Overall height	95 mm
Overall diameter	90 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class III
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%
Product Data	
Order product name	BGP312 5LED 3000K NB GG
Full product name	BGP312 5LED 3000K NB GG
Full product code	692382862983000
Order code	911401711652
Material Nr. (12NC)	911401711652
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828629830
Numerator - Packs per outer box	9
EAN/UPC - Case	6923828629830

## Dimensional drawing

