



Greenspace Flex

RS378B P6 940 PSU-E NB M55

Greenspace Flex, 6 W, 940 neutral white, Finger-protected

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

General Information		Operating and Electrical	
Number of gear units	1 unit	Input Voltage	220 to 240 V
Driver included	Yes	Line Frequency	50 or 60 Hz
Light source engine type	LED	Average CLO power consumption	470 W
CE mark	-	Power Consumption	6 W
Warranty period	3 years	Power Factor (Fraction)	0.9
Flammability mark	-	Connection	External connector
ENEC mark	-	Cable	-
Glow-wire test	Temperature 600 °C, duration 30 s	Number of products on MCB of 16 A type B	-
EU RoHS compliant	Yes		
Light Technical		Temperature	
Luminous Flux	492 lm	Ambient temperature range	-20 to +45 °C
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	82 lm/W	Controls and Dimming	
Color rendering index (CRI)	>90	Dimmable	No
Beam angle of light source	- degree(s)	Driver/power unit/transformer	Electronic transformer
Light source color	940 neutral white	Control interface	-
Optic type	-	Constant light output	No
Optical cover type	-		
		Mechanical and Housing	
		Housing Material	Aluminum Alloy

Greenspace Flex

Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	-
Fixation material	Aluminum
Housing Color	Dark gray
Optical cover finish	-
Overall height	49 mm
Overall diameter	55 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L80B50	50.000 hour(s)
---------------------------	----------------



Application Conditions

Maximum dim level	Not applicable
Suitable for random switching	No

Product Data

Order product name	RS378B P6 940 PSU-E NB M55
Full product name	RS378B P6 940 PSU-E NB M55
Full product code	911401720912
Order code	911401720912
Material Nr. (12NC)	911401720912
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48

Dimensional drawing



Modular Type	D, mm	H, mm
RS378B P6/P11 M55	55	49
RS378B P15 M55	55	49
RS378B P24 M70	70	90
RS378B P33 M87	87	107
RS378B P42 M102	102	116

