



Greenspace Flex

RS378B P6 940 PSU-E MB M55

Greenspace Flex, 6 W, 940 neutral white, 24°, Finger-protected

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

General Information		Luminaire light beam spread	
Number of gear units	1 unit	24°	
Driver included	Yes		
Light source engine type	LED	Operating and Electrical	
CE mark	-	Input Voltage	
Warranty period	3 years	220 to 240 V	
Flammability mark	-	Line Frequency	
ENEC mark	-	50 or 60 Hz	
Glow-wire test	Temperature 600 °C, duration 30 s	Average CLO power consumption	
EU RoHS compliant	Yes	470 W	
		Power Consumption	
		6 W	
		Power Factor (Fraction)	
		0.9	
		Connection	
		External connector	
		Cable	
		-	
		Number of products on MCB of 16 A type B	
		-	
Light Technical		Temperature	
Luminous Flux	492 lm	Ambient temperature range	
Correlated Color Temperature (Nom)	4000 K	-20 to +45 °C	
Luminous Efficacy (rated) (Nom)	82 lm/W		
Color rendering index (CRI)	>90	Controls and Dimming	
Beam angle of light source	- degree(s)	Dimmable	
Light source color	940 neutral white	No	
Optic type	-	Driver/power unit/transformer	
Optical cover type	-	Electronic transformer	
		Control interface	
		-	
		Constant light output	
		No	

Greenspace Flex

Mechanical and Housing	
Housing Material	Aluminum Alloy
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	-
Fixation material	Aluminum
Housing Color	Dark gray
Optical cover finish	-
Overall height	49 mm
Overall diameter	55 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Protection class IEC	Safety class II



Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Median useful life L80B50	50.000 hour(s)

Application Conditions	
Maximum dim level	Not applicable
Suitable for random switching	No

Product Data	
Order product name	RS378B P6 940 PSU-E MB M55
Full product name	RS378B P6 940 PSU-E MB M55
Full product code	692382864994499
Order code	911401720942
Material Nr. (12NC)	911401720942
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828649944
Numerator - Packs per outer box	48
EAN/UPC - Case	6923828652357

Dimensional drawing



Modular Type	D, mm	H, mm
RS378B P6/P11 M55	55	49
RS378B P15 M55	55	49
RS378B P24 M70	70	90
RS378B P33 M87	87	107
RS378B P42 M102	102	116

