



LED Wall Mount

BWS151 LED200/NW PSU 220-240V 7043

LED Low Power - 740 neutral white - Power supply unit - 50 to 60 Hz - Traffic gray B (7043)

People want to create a pleasant atmosphere around their property – something that will catch visitors’ attention, make them feel good and want to come back again. They would like to be able to create an appealing ambience at minimum cost, though without compromising on the quality of the lighting. Combining a simple round design with reliable lighting performance, this low-cost white-light LED wall fixture with opal diffuser delivers a soft light effect with attractive uniformity.

Product data

| General Information | |
|-------------------------------|---|
| Number of light sources | 96 pcs |
| Lamp family code | LED-LP [LED Low Power] |
| Light source color | 740 neutral white |
| Light source replaceable | No |
| Number of gear units | 1 unit |
| Driver/power unit/transformer | Power supply unit |
| Driver included | Yes |
| Optical cover/lens type | Polycarbonate bowl/cover UV-resistant |
| Control interface | - |
| Connection | Screw connection block |
| Cable | Cable without plug 2-pole |
| Protection class IEC | Safety class II |
| Flammability mark | For mounting on normally flammable surfaces |
| CE mark | CE mark |
| Warranty period | 1 years |

| RAL color | Traffic gray B (7043) |
|--|-----------------------|
| Constant light output | No |
| Number of products on MCB of 16 A type B | 1 |
| Light source engine type | LED |
| Operating and Electrical | |
| Input Voltage | 220 to 240 V |
| Input Frequency | 50 to 60 Hz |
| Power Factor (Min) | 0.4 |
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Housing Material | Polycarbonate |
| Optical cover/lens material | Polycarbonate |
| Mounting device | Allen screw fixation |

LED Wall Mount

| | |
|---------------------------|-----------|
| Optical cover/lens finish | Matte |
| Overall length | 200 mm |
| Overall width | 200 mm |
| Overall height | 62 mm |
| Color | Dark gray |

Approval and Application

| | |
|------------------------------|---|
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK08 [5 J vandal-protected] |

Initial Performance (IEC Compliant)

| | |
|-------------------------------------|------------|
| Initial luminous flux (system flux) | 250 lm |
| Luminous flux tolerance | +/-10% |
| Initial LED luminaire efficacy | 43.10 lm/W |
| Init. Corr. Color Temperature | 4000 K |
| Init. Color Rendering Index | >70 |

| | |
|-----------------------------|--------|
| Initial input power | 5.8 W |
| Power consumption tolerance | +/-10% |

Application Conditions


| | |
|---------------------------|---------------|
| Ambient temperature range | -20 to +40 °C |
|---------------------------|---------------|

Product Data

| | |
|---------------------------------|------------------------------------|
| Full product code | 911401724101 |
| Order product name | BWS151 LED200/NW PSU 220-240V 7043 |
| Order code | 911401724101 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 24 |
| Material Nr. (12NC) | 911401724101 |
| Net Weight (Piece) | 0.830 kg |



Dimensional drawing



BWS150 LED Wall mount

