



# LED Wall Mount

## BWS151 LED200/NW PSU 220-240V 9006

LED Wall Mount, 250 lm, 5.8 W, 740 neutral white, Safety class II, Allen screw fixation

People want to create a pleasant atmosphere around their property – something that will catch visitors' attention, make them feel good and want to come back again. They would like to be able to create an appealing ambience at minimum cost, though without compromising on the quality of the lighting. Combining a simple round design with reliable lighting performance, this low-cost white-light LED wall fixture with opal diffuser delivers a soft light effect with attractive uniformity.

### Product data

General Information		Light source color	
Lamp family code	LED-LP [LED Low Power]	740 neutral white	
Light source replaceable	No	Optical cover type	
Number of gear units	1 unit	Polycarbonate bowl/cover UV-resistant	
Driver included	Yes	Operating and Electrical	
Light source engine type	LED	Input Voltage	220 to 240 V
CE mark	CE mark	Line Frequency	50 to 60 Hz
Warranty period	1 years	Power Consumption	5.8 W
Flammability mark	For mounting on normally flammable surfaces	Power Factor (Fraction)	0.4
		Connection	Screw connection block
		Cable	Cable without plug 2-pole
		Number of products on MCB of 16 A type B 1	
Light Technical		Temperature	
Luminous Flux	250 lm	Ambient temperature range	-20 to +40 °C
Correlated Color Temperature (Nom)	4000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	43.10 lm/W	Dimmable	No
Color rendering index (CRI)	>70		
Number of light sources	96		

## LED Wall Mount

Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

### Mechanical and Housing

Housing Material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Aluminum and white
Mounting device	Allen screw fixation
Optical cover finish	Matte
Overall length	200 mm
Overall width	200 mm
Overall height	62 mm
Dimensions (Height x Width x Depth)	62 x 200 x 200 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Protection class IEC	Safety class II
----------------------	-----------------

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

### Product Data

Order product name	BWS151 LED200/NW PSU 220-240V 9006
Full product name	BWS151 LED200/NW PSU 220-240V 9006
Full product code	872016953230499
Order code	911401724201
Material Nr. (12NC)	911401724201
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169532304
Numerator - Packs per outer box	24
EAN/UPC - Case	8720169543799

### Dimensional drawing

