



UNIUrban

BGP461 LED120 WW 110-277V TS

UNIUrban, 12000 lm, 100 W, Tunable white, Safety class I, Side-entry for diameter 60 mm

UNIUrban is ideal for the urban lighting across the sidewalks, parks, gardens, residential areas, shopping center plazas. Its exquisite, stylish yet classic design is not only suitable for modern cities but also for historical architecture.

Product data

General Information	
Light source replaceable	No
Driver included	Yes
Light source engine type	LED
Value ladder	Performance
CE mark	CE mark
Flammability mark	-
Light Technical	
Luminous Flux	12,000 lm
Standard tilt angle posttop	15°
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	120 lm/W
Color rendering index (CRI)	≥70
Light source color	Tunable white
Optical cover type	Polycarbonate micro lens optic
Operating and Electrical	
Input Voltage	110 to 277 V
Line Frequency	50 to 60 Hz

Power Consumption	100 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 0.2 m without plug
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Optical cover material	Tempered glass
Housing Color	Grey
Mounting device	Side-entry for diameter 60 mm
Optical cover finish	Clear
Overall length	691 mm

Overall width	480 mm
Overall height	66 mm
Overall diameter	488 mm
Dimensions (Height x Width x Depth)	66 x 480 x 691 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	BGP461 LED120 WW 110-277V TS
Full product name	BGP461 LED120 WW 110-277V TS
Full product code	911401727582
Order code	911401727582
Material Nr. (12NC)	911401727582
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

