



# UniStrip G4

## BCP380 24LEDLP 27K 24V 40 L51

UniStrip G4, 297 lm, 5.6 W, Warm white, 40° x 40°, Safety class III, Mounting bracket adjustable

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

### Warnings and Safety

- For outdoor use only

### Product data

General Information	
Light source replaceable	No
Driver included	No
Light source engine type	LED
Lighting Technology	LED
CE mark	CE mark
Flammability mark	For mounting on normally flammable surfaces

Light Technical	
Luminous Flux	297 lm
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	53 lm/W

Color rendering index (CRI)	80
Light source color	Warm white
Optical cover type	Clear flat
Luminaire light beam spread	40° x 40°

Operating and Electrical	
Input Voltage	24 DC V
Line Frequency	- Hz
Power Consumption	5.6 W
Power Factor (Fraction)	0.9
Connection	2 Push-in connector 2-pole

UniStrip G4

Cable	2 cables 0.15m with connectors 2-pole
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Polycarbonate
Optical cover material	Tempered glass
Fixation material	Stainless steel
Housing Color	Dark gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Clear
Overall length	510 mm
Overall width	35 mm
Overall height	86 mm
Dimensions (Height x Width x Depth)	86 x 35 x 510 mm

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class III
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	4 SDCM
Power consumption tolerance	+/-10%
Product Data	
Order product name	BCP380 24LEDLP 27K 24V 40 L51
Full product name	BCP380 24LEDLP 27K 24V 40 L51
Full product code	911401738302
Order code	911401738302
Material Nr. (12NC)	911401738302
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30

Dimensional drawing

