



UniStrip G4

BCP382 12LED RGBNW 24V 30 L50 DMX

UniStrip G4, 666 lm, 18 W, Red, green, blue and white, 30° x 30°, Dynamic DMX, Safety class III, Mounting bracket adjustable

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Warnings and Safety

- For outdoor use only

Product data

General Information		Color rendering index (CRI)	
Light source replaceable	No	Light source color	Red, green, blue and white
Driver included	No	Optical cover type	Clear flat
Light source engine type	LED	Luminaire light beam spread	30° x 30°
Lighting Technology	LED	Operating and Electrical	
CE mark	CE mark	Input Voltage	24 DC V
Flammability mark	For mounting on normally flammable surfaces	Line Frequency	- Hz
Light Technical		Power Consumption	18 W
Luminous Flux	666 lm	Power Factor (Fraction)	0.9
Correlated Color Temperature (Nom)	-	Connection	2 Push-in connector 5-pole
Luminous Efficacy (rated) (Nom)	37 lm/W		

UniStrip G4

Cable	2 cables 0.15m with connectors 5-pole
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	Yes
Control interface	Dynamic DMX
Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Polymethyl methacrylate
Optical cover material	Tempered glass
Fixation material	Aluminum
Housing Color	Dark gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Clear
Overall length	500 mm
Overall width	38 mm
Overall height	47 mm
Dimensions (Height x Width x Depth)	47 x 38 x 500 mm

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class III

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	BCP382 12LED RGBNW 24V 30 L50 DMX
Full product name	BCP382 12LED RGBNW 24V 30 L50 DMX
Full product code	871951494472599
Order code	911401739112
Material Nr. (12NC)	911401739112
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514944725
Numerator - Packs per outer box	15
EAN/UPC - Case	8719514944725

Dimensional drawing

