



UniEdge

BCP390 4LED RGBNW 24V 3x90 DMX

UniEdge is a surface-mounted, exterior-rated and compact-sized architectural LED edge lighting luminaire that is designed for façade and outdoor decorative lighting applications. The robust mechanical and unique optical designs make UniEdge ideal for edges lighting on windows and doors inner frames, building façades, landmarks and monuments. Available in white, monochromatic colours, RGB, RGBW and tunable white. Unique spread lens with a DMX control option available to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Product data

General Information	
Lamp colour code	Red, green, blue and white (RGBW)
Light source replaceable	No
Driver included	No
Optical cover/lens type	CLFT [Clear flat]
Luminaire light beam spread	3° x 90°
Control interface	Dynamix DMX
Connection	2 push-in connectors 5-pole
Cable	2 cables 0.3 m with connector 5-pole
Protection class IEC	Safety class III (III)
Flammability mark	F [For mounting on normally flammable surfaces]
CE mark	CE mark
LED engine type	LED
Light Technical	
Standard tilt angle post-top	-
Operating and Electrical	
Input voltage	24 DC V

Input frequency	- Hz
Power factor (min.)	0.9
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing material	Aluminum die-cast
Optic material	Polycarbonate
Optical cover/lens material	Tempered glass
Fixation material	Aluminium
Mounting device	MBA [Mounting bracket adjustable]
Optical cover/lens finish	Clear
Overall length	181 mm
Overall width	51 mm
Overall height	58 mm
Colour	Dark Grey

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]

Initial Performance (IEC Compliant)

Initial luminous flux	102 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	10.2 lm/W
Lamp colour temperature	- K
Colour Rendering Index	-
Initial chromaticity	-
Initial input power	10 W
Power consumption tolerance	+/-10%

Application Conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Maximum dimming level	13%
-----------------------	-----


Product Data

Full product code	911401739812
Order product name	BCP390 4LED RGBNW 24V 3x90 DMX
Order code	911401739812
Numerator – quantity per pack	1
Numerator – packs per outer box	24
Material no. (12NC)	911401739812
Net weight (piece)	0.799 kg



Warnings and Safety

Dimensional drawing



UniEdge BCP390

