



# UniFlood C

## BVP324 54LED RGB 220V 8 DMX

UniFlood C, 4930 lm, 110 W, Red, green and blue, 8°, Dynamic DMX/RDM, Safety class I, Mounting bracket adjustable

UniFlood C is a circular shaped, exterior-rated and cost-effective architectural LED floodlight that is designed for façade, landscape and outdoor flood lighting applications. The robust mechanical design and high-efficiency optical design make it ideal for illuminating multi-story exterior facades, bridges, landmarks and monuments. Available in white, monochromatic colors, RGB, RGBW and tunable white. Six different spread lenses ranging from narrow spot to wide flood and DMX512/RDM control option available to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

### Warnings and Safety

- For outdoor use only

### Product data

General Information		Correlated Color Temperature (Nom)	
Light source replaceable	No	Luminous Efficacy (rated) (Nom)	45 lm/W
Number of gear units	1 unit	Color rendering index (CRI)	-
Driver included	Yes	Light source color	Red, green and blue
Light source engine type	LED	Optical cover type	Flat glass
Lighting Technology	LED	Luminaire light beam spread	8°
CE mark	CE mark	Operating and Electrical	
Flammability mark	For mounting on normally flammable surfaces	Input Voltage	220 to 240 V
Light Technical		Line Frequency	50 to 60 Hz
Luminous Flux	4,930 lm	Inrush current	70 A
		Inrush time	0.65 ms

UniFlood C

Power Consumption	110 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires and 2 Push-in connector 4-pole
Cable	Cable 0.5 m without plug 3-pole and 2 Cables 0.5 m with connector 4-pole
Number of products on MCB of 16 A type B 3	

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DMX interface
Control interface	Dynamic DMX/RDM
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Optic material	Polymethyl methacrylate
Optical cover material	Tempered glass
Fixation material	Steel
Housing Color	Dark gray
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	390 mm

Overall width	332 mm
Overall height	183 mm
Overall diameter	332 mm
Dimensions (Height x Width x Depth)	183 x 332 x 390 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Application Conditions

Maximum dim level	1%
-------------------	----

Product Data

Order product name	BVP324 54LED RGB 220V 8 DMX
Full product name	BVP324 54LED RGB 220V 8 DMX
Full product code	911401741052
Order code	01741052
Material Nr. (12NC)	911401741052
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



