



UniStrip G4

BCP385 12LED RGBNW 220V A7 L100 DMX

UniStrip G4 is a surface-mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications.;One family that fits all your needs, wall washing, grazing and also linear flood lighting.;The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution.;Available in white, monochromatic colours, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Product data

| General Information | |
|-------------------------------|--|
| Lamp colour code | - |
| Light source replaceable | No |
| Number of gear units | 1 unit |
| Driver/power unit/transformer | PSU [Power supply unit] |
| Driver included | Yes |
| Optical cover/lens type | GT [Tempered glass] |
| Luminaire light beam spread | 15° x 40° |
| Control interface | Dynamix DMX |
| Connection | Flying leads/wires and 2 push-in connectors 4-pole |
| Cable | Cable 0.3 m without plug 3-pole + 2 cables 0.3 m with connector 4-pole |
| Protection class IEC | Safety class I (I) |
| Flammability mark | F [For mounting on normally flammable surfaces] |
| CE mark | CE mark |
| Outdoor optic type | Asymmetrical |
| Number of products on MCB | 3 |
| LED engine type | LED |

| Light Technical | |
|--------------------------------|-------------------------|
| Standard tilt angle post-top | - |
| Standard tilt angle side entry | - |
| Operating and Electrical | |
| Input voltage | 220 to 240 V |
| Input frequency | 50 to 60 Hz |
| Inrush current | 70 A |
| Inrush time | 0.65 ms |
| Power factor (min.) | 0.9 |
| Controls and Dimming | |
| Dimmable | Yes |
| Mechanical and Housing | |
| Housing material | Aluminum extruded |
| Optic material | Polymethyl methacrylate |
| Optical cover/lens material | Glass |
| Fixation material | Aluminium |

UniStrip G4

| | |
|---------------------------|------------------------------------|
| Mounting device | MBA [Mounting bracket adjustable] |
| Optical cover/lens shape | Flat |
| Optical cover/lens finish | Clear |
| Overall length | 1000 mm |
| Overall width | 88 mm |
| Overall height | 158 mm |
| Colour | Dark Grey |

Approval and Application

| | |
|------------------------------|---|
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK06 [1 J] |

Initial Performance (IEC Compliant)

| | |
|--------------------------------|---------|
| Initial luminous flux | 3047 lm |
| Luminous flux tolerance | +/-10% |
| Initial LED luminaire efficacy | 30 lm/W |
| Lamp colour temperature | - K |
| Initial input power | 100 W |

| | |
|-----------------------------|--------|
| Power consumption tolerance | +/-10% |
|-----------------------------|--------|

Application Conditions

| | |
|---------------------------|---------------|
| Ambient temperature range | -40 to +50 °C |
| Maximum dimming level | 10% |


Product Data

| | |
|---------------------------------|-------------------------------------|
| Full product code | 911401752192 |
| Order product name | BCP385 12LED RGBNW 220V A7 L100 DMX |
| Order code | 911401752192 |
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 2 |
| Material no. (12NC) | 911401752192 |
| Net weight (piece) | 3.949 kg |



Warnings and Safety

Dimensional drawing



BCP280/383/384/385 UNIStrip G3

