



# Uni DMX controls and accessories

## ZXP399 main controller DMX

Uni DMX controls and accessories, 90 to 264 V, 50 to 60 Hz, Finger-protected, CE mark, Black

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar). DMX Controls include main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device. Main Controller: Industrial computer that can control up to 6000 DMX universes. Stand-alone Controller: Fits for medium applications with up to 700 DMX universes. Wiring accessories include leader and jumper cables with male and female IP67 connectors and end-caps. Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes. DMX Amplifier: Compact, IP65 and low power repeater that can amplify the DMX signal for up 100 meters.

### Product data

General Information		Overall height		177 mm
Accessory color	Black	Dimensions (Height x Width x Depth)		177 x 361 x 482 mm
CE mark	CE mark			
Operating and Electrical		Approval and Application		
Input Voltage	90 to 264 V	Ingress protection code		IP20 [Finger-protected]
Line Frequency	50 to 60 Hz			
Mechanical and Housing		Product Data		
Overall length	482 mm	Order product name		ZXP399 main controller DMX
Overall width	361 mm	Full product name		ZXP399 main controller DMX
		Full product code		871951494685900
		Order code		911401756612

Uni DMX controls and accessories

Material Nr. (12NC)	911401756612
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514946859
Numerator - Packs per outer box	1

EAN/UPC - Case	8719514946859
----------------	---------------

Dimensional drawing

