



ZXP399 DMX Controls and Accessories

ZXP399 sub-controller 12V 8 port DMX/RDM

12 DC V - - Hz - Finger-protected - CE mark

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar).;DMX Controls include main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device.;Main Controller: Industrial computer that can control up to 6000 DMX universes.;Stand-alone Controller: Fits for medium applications with up to 700 DMX universes.;Wiring accessories include leader and jumper cables with male and female IP67 connectors and end-caps.;Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes.;DMX Amplifier: Compact, IP65 and low power repeater that can amplify the DMX signal for up to 100 meters.

Product data

General Information	
CE mark	CE mark
Accessory color	Black
Operating and Electrical	
Input Voltage	12 DC V
Input Frequency	- Hz

Mechanical and Housing	
Overall length	277.6 mm
Overall width	193 mm
Overall height	66 mm
Dimensions (Height x Width x Depth)	66 x 193 x 278 mm (2.6 x 7.6 x 10.9 in)
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

ZXP399 DMX Controls and Accessories


Product Data

Full product code	911401756672
Order product name	ZXP399 sub-controller 12V 8 port DMX/RDM
Order code	911401756672
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Material Nr. (12NC)	911401756672
Net Weight (Piece)	1.499 kg

IP 20

Dimensional drawing



ZXP399

