



UNIUrban

BGP461 LED78 NW 230V SR TS 7P Spg77

UNIUrban, 7800 lm, 65 W, 740 neutral white, Safety class I

UNIUrban is ideal for urban lighting across pathways, parks, gardens, residential areas and shopping centre areas. Its exquisite, stylish yet classic design is not only suitable for modern cities but also for historical architecture.

Product data

General Information	
Driver included	Yes
Value ladder	Performance
CE mark	CE mark
Flammability mark	For mounting on normally flammable surfaces
Light Technical	
Luminous Flux	7,800 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	120 lm/W
Color rendering index (CRI)	>70
Light source color	740 neutral white
Optical cover type	Acrylate micro-lens optic
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 or 60 Hz
Power Consumption	65 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires

Cable	Cable 0.2 m without plug
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	Yes
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Glass
Housing Color	Aluminum and gray
Overall length	692 mm
Overall width	482 mm
Overall height	66 mm
Effective projected area	0.045 m²
Dimensions (Height x Width x Depth)	66 x 482 x 692 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM ≤ 5
Power consumption tolerance	+/-10%

Product Data

Order product name	BGP461 LED78 NW 230V SR TS 7P Spg77
--------------------	-------------------------------------

Full product name	BGP461 LED78 NW 230V SR TS 7P Spg77
Full product code	911401759262
Order code	911401759262
Material Nr. (12NC)	911401759262
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

