



# Flex Cove G4

## LS170S LED16 840 IP20 L5000

Flex Cove G4, 1600 lm, 100 lm/W, 840 neutral white, 24 DC V,  
Finger-protected

Sustainable and flexible offering with excellent optical performance

### Product data

General Information	
Light source replaceable	No
Number of gear units	-
Driver included	No
Light source engine type	-
Glow-wire test	-
Flammability mark	-
CE mark	-
ENEC mark	-
Warranty period	3 years
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	1,600 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	80
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	Symmetrical
Optical cover type	-

Luminaire light beam spread	120°
Operating and Electrical	
Input Voltage	24 DC V
Line Frequency	- Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Power Consumption	72 W
Power Factor (Fraction)	1
Connection	Connection unit 2-pole
Cable	2 cables without plug 1-pole
Number of products on MCB of 16 A type B	-
Temperature	
Ambient temperature range	-20 to +35 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	-
Control interface	-
Constant light output	No

Flex Cove G4

Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	-
Optical cover material	-
Fixation material	-
Housing Color	White
Optical cover finish	-
Overall length	5,000 mm
Overall width	10 mm
Overall height	1.4 mm
Dimensions (Height x Width x Depth)	1 x 10 x 5000 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK00 [No protection]
Protection class IEC	Safety class III
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Initial chromaticity	0.38;0.38; SDCM 3
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	30,000 hour(s)
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	LS170S LED16 840 IP20 L5000
Full product name	LS170S LED16 840 IP20 L5000
Full product code	911401759532
Order code	911401759532
Material Nr. (12NC)	911401759532
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

Dimensional drawing

