PHILIPS

Lighting



Coreview Troffer G3

RC420B LED50S/840 PSU W60L120 GM

Coreview Troffer G3, 100 lm/W, 840 neutral white

Indirect LED troffer delivering soft and uniform light with visual comfort

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Warranty period	3 years
Glow-wire test	Temperature 600 °C, duration 30 s

Light Technical	
Luminous Flux	3,600 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Optic type	Wide beam
Optical cover type	Opal
Luminaire light beam spread	120°

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	22 A
Inrush time	2,750 ms
Power Consumption	36 W
Power Factor (Fraction)	0.9
Connection	Internal connector
Number of products on MCB of 16 A type B	24

Temperature	
Ambient temperature range	-20 to +40 °C

Controls and Dimming	
Dimmable	Yes
Control interface	-

Coreview Troffer G3

Constant light output	No

Mechanical and Housing

Housing Material	Metal
Optic material	Polystyrene
Optical cover material	Polymethyl methacrylate
Fixation material	Steel
Housing Color	White
Optical cover finish	Opal
Overall length	597 mm
Overall width	597 mm
Overall height	121 mm
Dimensions (Height x Width x Depth)	121 x 597 x 597 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM<4
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)


Application Conditions

Maximum dim level	1%

Product Data

Order product name	RC420B LED50S/840 PSU W60L120 GM
Full product name	RC420B LED50S/840 PSU W60L120 GM
Full product code	872016972494599
Order code	72494599
Material Nr. (12NC)	911401803597
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169724945
Numerator - Packs per outer box	2
EAN/UPC - Case	8720169724945

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.