



Solar Panel Sub System

100W 17V Panel subsystem Vmpp 18.22V

A Range of Solar panels from 20 W to 325 W specially designed for Philips Solar Street lighting, Flood lighting and Solar Indoor Systems

Product data

General Information	
CE mark	CE mark
Warranty period	3 years
Operating and Electrical	
Panel type	Poly crystalline
Panel voltage	17 V
Panel peak wattage	100 W
Cable connection kit	Included
Cable	Cable 1.0 m 4.0 sqmm with Molex Connectors
Temperature	
Ambient temperature range	-40 to +85 °C
Mechanical and Housing	
Overall length	990 mm
Overall width	666 mm
Overall height	35 mm

Dimensions (Height x Width x Depth)	35 x 666 x 990 mm
Approval and Application	
Ingress protection code	IP67 [Dust penetration-protected, watertight]
Product Data	
Order product name	100W 17V Panel subsystem Vmpp 18.22V
Full product name	100W 17V Panel subsystem Vmpp 18.22V
Full product code	872016951899599
Order code	911401803702
Material Nr. (12NC)	911401803702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169518995
Numerator - Packs per outer box	30
EAN/UPC - Case	8720169518995

Solar Panel Sub System

Dimensional drawing

