



Solar Panel Sub System

155W 17V Panel subsystem Vmpp 18.93V

A Range of Solar panels from 20 W to 325 W specially designed for Philips Solar Street lighting, Flood lighting and Solar Indoor Systems

Product data

General Information	
CE mark	CE mark
Warranty period	3 years
Operating and Electrical	
Panel type	Poly crystalline
Panel voltage	17 V
Panel peak wattage	155 W
Cable connection kit	Included
Cable	Cable 1.0 m 4.0 sqmm with Molex Connectors
Temperature	
Ambient temperature range	-40 to +85 °C
Mechanical and Housing	
Overall length	1,476 mm
Overall width	666 mm
Overall height	35 mm

Dimensions (Height x Width x Depth)	35 x 666 x 1476 mm
Approval and Application	
Ingress protection code	IP67 [Dust penetration-protected, watertight]
Product Data	
Order product name	155W 17V Panel subsystem Vmpp 18.93V
Full product name	155W 17V Panel subsystem Vmpp 18.93V
Full product code	872016972923099
Order code	911401803902
Material Nr. (12NC)	911401803902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169729230
Numerator - Packs per outer box	30
EAN/UPC - Case	8720169729230

Solar Panel Sub System

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, December 21 - data subject to change