



Solar Panel Sub System

200W 36V Panel subsystem Vmpp 38.99V

A Range of Solar panels from 20 W to 325 W specially designed for Philips Solar Street lighting, Flood lighting and Solar Indoor Systems

Product data

General Information	
CE mark	CE mark
Warranty period	3 years
Operating and Electrical	
Panel type	Poly crystalline
Panel voltage	36 V
Panel peak wattage	200 W
Cable connection kit	Included
Cable	Cable 1.0 m 4.0 sqmm with Molex Connectors
Temperature	
Ambient temperature range	-40 to +85 °C
Mechanical and Housing	
Overall length	1,318 mm
Overall width	992 mm
Overall height	40 mm

Dimensions (Height x Width x Depth)	40 x 992 x 1318 mm
Approval and Application	
Ingress protection code	IP67 [Dust penetration-protected, watertight]
Product Data	
Order product name	200W 36V Panel subsystem Vmpp 38.99V
Full product name	200W 36V Panel subsystem Vmpp 38.99V
Full product code	872016972924799
Order code	911401804102
Material Nr. (12NC)	911401804102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169729247
Numerator - Packs per outer box	30
EAN/UPC - Case	8720169729247

Solar Panel Sub System

Dimensional drawing

