



Solar Panel Sub System

260W 30V Panel subsystem Vmpp 30.72V

A Range of Solar panels from 20 W to 325 W specially designed for Philips Solar Street lighting, Flood lighting and Solar Indoor Systems

Product data

General Information	
CE mark	CE mark
Warranty period	3 years
Operating and Electrical	
Panel type	Poly crystalline
Panel voltage	30 V
Panel peak wattage	260 W
Cable connection kit	Included
Cable	Cable 1.0 m 4.0 sqmm with Molex Connectors
Temperature	
Ambient temperature range	-40 to +85 °C
Mechanical and Housing	
Overall length	1,640 mm
Overall width	992 mm

Overall height	40 mm
Dimensions (Height x Width x Depth)	40 x 992 x 1640 mm
Approval and Application	
Ingress protection code	IP67 [Dust penetration-protected, watertight]
Product Data	
Order product name	260W 30V Panel subsystem Vmpp 30.72V
Full product name	260W 30V Panel subsystem Vmpp 30.72V
Full product code	911401804302
Order code	911401804302
Material Nr. (12NC)	911401804302
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	26

Solar Panel Sub System

Dimensional drawing

