



SmartBright LED Batten G2

BN012C LED10/WW L600 G2

SmartBright LED Batten G2, 10 W, 1000 lm, 3000 K, Wide beam

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. This new batten range of LED products can be used to replace traditional battens with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch

Product data

| General Information | | | |
|------------------------------------|----------------------------------|--|---------------------------|
| Light source replaceable | No | Optical cover type | Polycarbonate linear |
| Number of gear units | 1 unit | Luminaire light beam spread | 140° |
| Driver included | Yes | Operating and Electrical | |
| Light source engine type | LED | Input Voltage | 220 to 240 V |
| CE mark | CE mark | Line Frequency | 50 to 60 Hz |
| Warranty period | 3 years | Power Consumption | 10 W |
| Glow-wire test | Temperature 650 °C, duration 5 s | Power Factor (Fraction) | 0.8 |
| EU RoHS compliant | Yes | Connection | Flying leads/wires |
| Light Technical | | Cable | Cable without plug 2-pole |
| Luminous Flux | 1,000 lm | Number of products on MCB of 16 A type B | 10 |
| Correlated Color Temperature (Nom) | 3000 K | Temperature | |
| Luminous Efficacy (rated) (Nom) | 100 lm/W | Ambient temperature range | +20 to +35 °C |
| Color rendering index (CRI) | >80 | Controls and Dimming | |
| Light source color | Warm white | Dimmable | No |
| Optic type | Wide beam | | |

SmartBright LED Batten G2

| | |
|-------------------------------|----------------------------|
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Control interface | - |
| Constant light output | No |

Mechanical and Housing

| | |
|-------------------------------------|------------------|
| Housing Material | Polyamide |
| Optic material | Polycarbonate |
| Optical cover material | Polyamide |
| Fixation material | Steel |
| Housing Color | White |
| Optical cover finish | Clear |
| Overall length | 600 mm |
| Overall width | 30 mm |
| Overall height | 37 mm |
| Dimensions (Height x Width x Depth) | 37 x 30 x 600 mm |

Approval and Application

| | |
|------------------------------|-------------------------|
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK00 [No protection] |
| Protection class IEC | Safety class II |

Initial Performance (IEC Compliant)

| | |
|-------------------------|--------|
| Luminous flux tolerance | +/-10% |
|-------------------------|--------|

| | |
|-----------------------------|--------|
| Initial chromaticity | SDCM<6 |
| Power consumption tolerance | +/-10% |

Over Time Performance (IEC Compliant)

| | |
|---------------------------|----------------|
| Median useful life L70B50 | 25,000 hour(s) |
|---------------------------|----------------|

Application Conditions

| | |
|-------------------|----------------|
| Maximum dim level | Not applicable |
|-------------------|----------------|

Product Data

| | |
|---------------------------------|-------------------------|
| Order product name | BN012C LED10/WW L600 G2 |
| Full product name | BN012C LED10/WW L600 G2 |
| Full product code | 911401806997 |
| Order code | 911401806997 |
| Material Nr. (12NC) | 911401806997 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8710163308050 |
| Numerator - Packs per outer box | 25 |
| EAN/UPC - Case | 8710163308357 |

Dimensional drawing

