

Lighting

PHILIPS

SmartBright LED Batten G2

BN012C LED10/NW L600 AU G2

SmartBright LED Batten G2, 10 W, 1000 lm, 4000 K, Wide beam

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. This new batten range of LED products can be used to replace traditional battens with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Warranty period	3 years
Glow-wire test	Temperature 750 °C, duration 5 s
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	1,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	>80
Light source color	Neutral white
Optic type	Wide beam

Optical cover type	Polycarbonate linear
Luminaire light beam spread	140°
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	6.23 A
Inrush time	0.0442 ms
Power Consumption	10 W
Power Factor (Fraction)	0.8
Connection	Flying leads/wires
Cable	Cable without plug 2-pole
Number of products on MCB of 16 A type B	10
Temperature	
Ambient temperature range	+20 to +35 °C

SmartBright LED Batten G2

No
Power supply unit (On/Off)
-
No
Polyamide
Polycarbonate
Polyamide
Steel
White
Clear
600 mm
30 mm
37 mm
37 x 30 x 600 mm
IP20 [Finger-protected]
IK00 [No protection]

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<6
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	25,000 hour(s)
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	BN012C LED10/NW L600 AU G2
Full product name	BN012C LED10/NW L600 AU G2
Full product code	911401808297
Order code	911401808297
Material Nr. (12NC)	911401808297
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163308180
Numerator - Packs per outer box	12
EAN/UPC - Case	8710163308487

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, October 30 - data subject to change