



# Smartbright CCT Tunable Panel

## RC170B LED38S/SCCT PSU W30L120 AU

Smartbright CCT Tunable Panel, 100 lm/W, White

The new Philips tri-colour slim panel offers exceptional value. It is Perfect for your everyday ceiling lighting installations, available in 2 standard sizes and comes with option of 3 CCT selection switch for customer.

### Product data


General Information		Operating and Electrical	
Light source replaceable	No	Light source color	White
Number of gear units	1 unit	Optic type	Beam angle 110°
Driver included	Yes	Optical cover type	Opal
Light source engine type	LED	Luminaire light beam spread	110°
Service tag	Yes		
CE mark	-	Input Voltage	220 to 240 V
Warranty period	5 years	Line Frequency	50 or 60 Hz
Flammability mark	-	Initial CLO power consumption	- W
ENEC mark	-	Average CLO power consumption	- W
Glow-wire test	Temperature 650 °C, duration 30 s	Inrush current	3.5 A
EU RoHS compliant	No	Inrush time	0.046 ms
		Power Consumption	38 W
		Power Factor (Fraction)	0.9
		Connection	Connection unit 2-pole
		Cable	-
		Number of products on MCB of 16 A type B	74
Light Technical			
Luminous Flux	3,800 lm		
Correlated Color Temperature (Nom)	4000 5000 6500 K		
Luminous Efficacy (rated) (Nom)	100 lm/W		
Color rendering index (CRI)	>80		
Beam angle of light source	110 degree(s)		

Smartbright CCT Tunable Panel

Temperature	
Ambient temperature range	-10 to +35 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum extruded
Reflector material	-
Optic material	Polystyrene
Optical cover material	Polystyrene
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	1,195 mm
Overall width	295 mm
Overall height	11 mm
Dimensions (Height x Width x Depth)	11 x 295 x 1195 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	0.3818;0.3797
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.0029 %
Median useful life L70B50	55,000 hour(s)
Median useful life L80B50	33,000 hour(s)
Median useful life L90B50	16,000 hour(s)
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	RC170B LED38S/SCCT PSU W30L120 AU
Full product name	RC170B LED38S/SCCT PSU W30L120 AU
Full product code	871016334343399
Order code	911401813080
Material Nr. (12NC)	911401813080
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163343433
Numerator - Packs per outer box	4
EAN/UPC - Case	8710163343457

Dimensional drawing



## Smartbright CCT Tunable Panel

