



Greenperform Batten

BN208C LED40/NW L1200 PSD ACF EN

Greenperform Batten, 34 W, 4000 lm, 4000 K, Wide beam, DALI

GreenPerform Batten BN208C Dali is a high quality LED batten that delivers significant energy savings of up to 50% comparing to conventional T8 battens. BN208X incorporates the reliable structure, long lifetime LED lighting, and the global standard ZigBee control system, to achieve an easy-to-use networked solution. In the mean time, it helps to further increase energy saving maximum to 80% with daylight harvest and occupancy sensor.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information		Light Technical	
Lamp family code	LED40S [LED module, system flux 4000 lm]	Luminous Flux	4,000 lm
Light source replaceable	No	Correlated Color Temperature (Nom)	4000 K
Number of gear units	1 unit	Luminous Efficacy (rated) (Nom)	118 lm/W
Gear	-	Color rendering index (CRI)	80
Driver included	Yes	Light source color	Neutral white
Light source engine type	LED	Optic type	Wide beam
CE mark	CE mark	Optical cover type	Opal
Flammability mark	-	Luminaire light beam spread	110°
ENEC mark	-	Operating and Electrical	
Glow-wire test	Temperature 650 °C, duration 30 s	Input Voltage	220 to 240 V
		Line Frequency	50 to 60 Hz

Greenperform Batten

Power Consumption	34 W
Power Factor (Fraction)	0.9
Connection	Screw connection block 3-pole
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	Yes

Mechanical and Housing

Housing Material	Steel
Optic material	Polycarbonate
Optical cover material	Polymethyl methacrylate
Housing Color	White
Optical cover finish	Opal

Approval and Application

Ingress protection code	IP20 [Finger-protected]
-------------------------	-------------------------

Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7.5%
Initial chromaticity	-
Power consumption tolerance	+/-10%

Application Conditions

Maximum dim level	1% (depends on dimmer, ELV)
-------------------	-----------------------------

Product Data

Order product name	BN208C LED40/NW L1200 PSD ACF EN
Full product name	BN208C LED40/NW L1200 PSD ACF EN
Full product code	911401830999
Order code	911401830999
Material Nr. (12NC)	911401830999
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

—

