



Ledinaire Batten

BN013C LED10S/830 L600

830 warm white

The Ledinaire range contains a selection of popular off-the-shelf LED luminaires that comes with high Philips quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need. Both integrated (BN012C) and TLED-based (BN060C) versions are available

Product data

General Information	
Beam angle of light source	- °
Light source colour	830 warm white
Cap base	G13 [Medium Bi-Pin Fluorescent]
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Optic type	VWB [Very wide beam]
Luminaire light beam spread	154°
Control interface	-
Connection	Push-in connector 2-pole
Cable	-
Protection class IEC	Safety class II
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	F [For mounting on normally flammable surfaces]
CE mark	CE mark
ENEC mark	-
Warranty period	5 years
Constant light output	No

Number of products on MCB	10
EU RoHS compliant	Yes
Unified glare rating CEN	26

Operating and Electrical

Input voltage	220 to 240 V
Input frequency	50 or 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	3.92 A
Inrush time	0.043 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Polycarbonate

Ledinaire Batten

Optical cover/lens material	Polycarbonate
Fixation material	-
Optical cover/lens finish	Opal
Overall length	612 mm
Overall width	30 mm
Overall height	36.5 mm
Colour	White
Dimensions (height x width x depth)	37 x 30 x 612 mm (1.4 x 1.2 x 24.1 in)

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux	940 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	100 lm/W
Init. Corr. Colour Temperature	3000 K
Init. colour rendering index	≥80
Initial chromaticity	0.4282, 0.3979, SDCM≤5
Initial input power	10 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	7.50 %
--	--------

Lumen maintenance at median useful life*	L65
50,000 h	

Application Conditions


Ambient temperature range	-20 to +35 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	Not applicable
Suitable for random switching	Not applicable

Product Data

Full product code	871016334955899
Order product name	BN013C LED10S/830 L600
EAN/UPC – product	8710163349558
Order code	34955899
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	911401836080
Net weight (piece)	0.150 kg



Dimensional drawing



Batten BN060C

Ledinaire Batten

